



## GROUNDING

GREAVES EXCLUSIVE

### Ground-Lok™ CLAMP SYSTEM SERRATED HEAD - (ASSEMBLED)



### BRONZE WATER PIPE GROUND CLAMPS

Copper wire only

NAED NUMBER	CATALOG NUMBER	INCLUDES ADAPTER TYPE	WATER PIPE SIZE	GROUND WIRE MAX	CTN QTY
30200	G 3		1/2" - 1"		25
30240	G 4	WIRE	1/4" - 2"	4/0 STR	20
30480	G 15	ADAPTER	2 1/2" - 4"		4
30500	G 16		4 1/2" - 6"		4
<b>FOR 1/2" RIGID CONDUIT</b>					
30280	G 5		1/2" - 1"		25
30320	G 6	1/2" CONDUIT	1/4" - 2"	2/0 STR	20
30520	G 18	SIZE	2 1/2" - 4"		4
30540	G 19		4 1/2" - 6"		4
<b>FOR 3/4" RIGID CONDUIT</b>					
30360	G 7		1/2" - 1"		25
30380	G 8	3/4" CONDUIT	1/4" - 2"	3/0 STR	20
30580	G 21	SIZE	2 1/2" - 4"		4
30600	G 22		4 1/2" - 6"		4
<b>FOR 1" RIGID CONDUIT</b>					
30400	G 9		1/2" - 1"		25
30420	G 10	1" CONDUIT	1/4" - 2"	3/0 STR	10
30620	G 24	SIZE	2 1/2" - 4"		2
30640	G 25		4 1/2" - 6"		2

PLATING: For tin-plating add suffix letter "P" to catalog numbers.  
UL listed to #4 AWG. CSA certified as shown.



### Ground-Lok™ CLAMP SYSTEM BRASS SCREWS



### G1BS SERIES

NAED NUMBER	CATALOG NUMBER	INCLUDES ADAPTER TYPE	WATER PIPE SIZE	GROUND WIRE MAX	CTN QTY
70560	G 1 BS	-	1/2" - 1"		50
70565	G 2 BS	-	1/4" - 2"	2 STR	25
70570	G 12 BS	-	2 1/2" - 4"		4
70575	G 13 BS	-	4 1/2" - 6"		4
70580	G 40 BS	Wire	-	4/0 STR	20
70585	G 41 BS	1/2" Conduit	-	2/0 STR	20
70590	G 42 BS	3/4" Conduit	-	3/0 STR	20
70600	G 43 BS	1" Conduit	-	3/0 STR	20
70566	G 3 BS	Wire	1/2" - 1"	4/0 STR	25
70567	G 4 BS	Wire	1/4" - 2"	4/0 STR	10

PLATING: For tin-plating add suffix letter "P" to catalog numbers. UL listed to #4 AWG.  
CSA certified as shown.



www.greaves-usa.com

Guilford, Connecticut 06437 Area Code 203-453-4304 - Fax 203-243-8343

TOLL FREE 1-800-243-1130 (Outside CT)