



COMPRESSION

BUTT SPLICES - COPPER

Produced from high conductivity seamless copper tubing

Marked with die index and color coded

Tin plated to provide corrosion resistance



SC SERIES

Standard Barrel

NAED NUMBER	CATALOG NUMBER	WIRE SIZE	U-TYPE DIE		CTN QTY	EST. SHIPPING	
			COLOR	INDEX		WEIGHT (lbs)	UNIT
51808	SC 8	#8	RED	6	100	1.22	CTN
51806	SC 6	#6	BLUE	7/374	100	2.04	CTN
51804	SC 4	#4	GRAY	8/346	100	2.55	CTN
51802	SC 2	#2	BROWN	10	50	2.01	CTN
51800	SC 1	#1	GREEN	11/375	50	2.16	CTN
51810	SC 10	1/0	PINK	12/348	50	2.66	CTN
51812	SC 20	2/0	BLACK	13	25	1.70	CTN
51814	SC 30	3/0	ORANGE	14	25	2.02	CTN
51816	SC 40	4/0	PURPLE	15	25	2.38	CTN
51818	SC 250	250	YELLOW	16	25	3.00	CTN
51820	SC 300	300	WHITE	17/298	12	1.64	CTN
51822	SC 350	350	RED	18/324	12	2.01	CTN
51824	SC 400	400	BLUE	19/470	6	1.24	CTN
51826	SC 500	500	BROWN	20/299	6	2.00	CTN
51828	SC 600	600	GREEN	22/472	6	2.51	CTN
51830	SC 750	750	BLACK	24/473	3	1.15	CTN
51832	SC 1000	1000	WHITE	27	3	2.64	CTN

For copper cable



600 V*

C SERIES

Long Barrel

NAED NUMBER	CATALOG NUMBER	WIRE SIZE	U-TYPE DIE		CTN QTY	EST. SHIPPING	
			COLOR	INDEX		WEIGHT (lbs)	UNIT
13005	C 8	#8	RED	6	100	2.30	CTN
13006	C 6	#6	BLUE	7/374	100	2.81	CTN
13004	C 4	#4	GRAY	8/346	100	3.42	CTN
13002	C 2	#2	BROWN	10	50	3.20	CTN
13000	C 1	#1	GREEN	11/375	50	3.26	CTN
13008	C 10	1/0	PINK	12/348	50	4.00	CTN
13010	C 20	2/0	BLACK	13	25	2.51	CTN
13012	C 30	3/0	ORANGE	14	25	2.90	CTN
13014	C 40	4/0	PURPLE	15	25	3.19	CTN
13016	C 250	250	YELLOW	16	25	4.80	CTN
13018	C 300	300	WHITE	17/298	12	2.66	CTN
13020	C 350	350	RED	18/324	12	3.59	CTN
13022	C 400	400	BLUE	19/470	6	2.00	CTN
13024	C 500	500	BROWN	20/299	6	3.11	CTN
13026	C 600	600	GREEN	22/472	6	4.80	CTN
13028	C 750	750	BLACK	24/473	3	3.00	CTN
13030	C 1000	1000	White	27	3	4.32	CTN



600 V*

For heavy duty applications

*May be used for applications up to 35 KV when proper installation and insulation procedures are employed.