

B11 4.5W DIM. E26 TITANIUM LED SERIES 4.0



PRO



4.5W REPLACES



**40W
Inc.**

80% Energy Savings

\$113 Savings
per lamp*

- ⌚ Omnidirectional: 275° beam angle
- ⌚ High efficacy 70 LPW in Warm White
- ⌚ E26 base for various applications
- ⌚ Compact heat sink blends in with fixtures
- ⌚ Energy efficient alternative to incandescent candle lighting
- ⌚ Smooth dimming with existing installations



25,000 H



DIMMABLE



70
LPW
EFFICACY



WARRANTY



CRI (Ra)



OMNI
DIRECTIONAL



LM 79

LM 80

TM 21

IES



SUITABLE FOR ALL DECORATIVE APPLICATIONS



B11 4.5W DIM. E26 TITANIUM LED SERIES 4.0



APPLICATIONS

Chandelier



Sconce



Uplighting



#DS046-B11-4.5W-E26

SPECIFICATIONS

Product Model	40728 4.5B11G4DIM/827/E26
Type	B11 (candle)
Base	E26
Power (W)	4.5
Voltage - Frequency	120V 60Hz
Color Temp. (ANSI)	Warm White 2700K
CRI (Ra)	80
Typical lumens (lm)	315
Efficacy (LPW)	70
Beam Angle	275°
Dimmable	Yes**
Power Factor	0.9
Rated Lifetime - L70 (hrs.)	25,000
Dia. x MOL	1.38"x4.17" (35x106mm)
Weight (lb. / g)	.1lb / 45g

* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 25,000-hr lifetime

** List of tested dimmer switches available on website

*** Not intended for use in totally enclosed fixtures

**** Suitable for damp locations. Not for use where directly exposed to weather or water