

APPLICATIONS

General Lighting



Downlighting



Uplighting



Ref.#:DS001-A19-9W

SPECIFICATIONS

Product Model	40741 9A19G4DIM/824	40742 9A19G4DIM/827	40743 9A19G4DIM/830	40744 9A19G4DIM/840
Type	A19	A19	A19	A19
Base	E26	E26	E26	E26
Power (W)	9	9	9	9
Voltage - Frequency	120V 60Hz	120V 60Hz	120V 60Hz	120V 60Hz
Color Temp. (ANSI)	Extra Warm White 2400K	Warm White 2700K	Warm White 3000K	Natural White 4000K
CRI (Ra) (typ.)	80	80	80	80
Typical lumens (lm)	700	800	800	850
Efficacy (LPW)	78	89	89	94
Beam Angle	300°	300°	300°	300°
Dimmable	Yes**	Yes**	Yes**	Yes**
Power Factor	0.9	0.9	0.9	0.9
Rated Lifetime - L70 (hrs.)	25,000	25,000	25,000	25,000
Dia. x MOL	2.36"x4.57" (60x116mm)	2.36"x4.57" (60x116mm)	2.36"x4.57" (60x116mm)	2.36"x4.57" (60x116mm)
Weight (lb. / g)	0.26lb. / 118g	0.26lb. / 118g	0.26lb. / 118g	0.26lb. / 118g

* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 25,000-hr lifetime

** List of tested dimmer switches available on website

*** Not intended for use in enclosed fixtures

**** Suitable for damp locations. Not for use where directly exposed to weather or water