

# A19 9.5W WARM DIM. TITANIUM LED SERIES



## APPLICATIONS

### General Lighting



### Downlighting



### Uplighting



Ref.:# DS145-A19-9.5W-WARM-DIM

## SPECIFICATIONS

Product Model	57883 9.5A19DIM/8CCTD
Type	A19
Base	E26
Power (W)	9.5
Voltage - Frequency	120V 60Hz
Color Temp. (ANSI)	Amber White-Soft White 2200K-2700K
CRI (Ra) (typ.)	80
Typical lumens (lm)	800
Efficacy (LPW)	84
Beam Angle	330°
Dimmable	Yes**
Power Factor	0.9
Rated Lifetime - L70 (hrs.)	25,000
Dia. x MOL	2.36"x4.61" (60x117mm)
Weight (lb. / g)	0.17lb. / 77g

\* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 25,000-hr lifetime

\*\* List of tested dimmer switches available on website

\*\*\* Not intended for use in totally enclosed fixtures

\*\*\*\* Suitable for damp locations. Not for use where directly exposed to weather or water