

# B10 3.5W FILAMENT DIM. TITANIUM LED SERIES



PRO



3.5W REPLACES



**40W  
Inc.**

80% Energy Savings

**\$74** Savings  
per lamp\*

- Ⓞ Omnidirectional: 320° beam angle
- Ⓞ Exceptional efficacy 80 LPW in Soft White
- Ⓞ Micro-designed driver - No heatsink required
- Ⓞ Comfortable warm diffused light
- Ⓞ Vintage candle look fits all applications
- Ⓞ Smooth dimming with existing installations



15,000 H



DIMMABLE



EFFICACY



WARRANTY



CRI (Ra)



OMNI DIRECTIONAL



LM 79

LM 80

TM 21



## FILAMENT PRODUCT FEATURES



The GREEN CREATIVE Filament Series features a wide variety of vintage style bulbs that use the latest in LED technology. Each filament bulb uses a high quality LED package which results in longer lifetimes and higher efficacies. Each lamp's micro-designed driver provides excellent dimming performance without the need for a heat.

# B10 3.5W FILAMENT DIM. TITANIUM LED SERIES



## APPLICATIONS

### Chandelier Lighting



### General Lighting



### Ambient Lighting



Ref.#: DS235-B10-F-3.5W-DIM-A-R-130417

## SPECIFICATIONS

Product Model	58010 3.5FBA10DIM/824/FT/A/R
Type	BA10
Base	E12
Power (W)	3.5
Voltage - Frequency	120V 60Hz
Color Temp. (ANSI)	Extra Warm White 2400K
CRI (Ra)	80
Typical lumens (lm)	280
Efficacy (LPW)	80
Beam Angle	320°
Dimmable	Yes**
Power Factor	0.9
Rated Lifetime - L70 (hrs.)	15,000
Dia. x MOL	1.26"x4.09" (32x104mm)
Weight (lb. / g)	0.03lb. / 14g

\* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 15,000-hr lifetime

\*\* List of tested dimmer switches available on website

\*\*\* Suitable for damp locations. Not for use where directly exposed to weather or water