

G25 4.5W FILAMENT DIM. TITANIUM LED SERIES



PRO



4.5W REPLACES



**40W
Inc.**

80% Energy Savings

\$76 Savings
per lamp*

- ⌚ Omnidirectional: 330° beam angle
- ⌚ High efficacy 100 LPW in Soft White
- ⌚ Micro-designed driver - No heatsink required
- ⌚ Comfortable warm diffused light
- ⌚ Vintage globe look fits all applications
- ⌚ Smooth dimming with existing installations



15,000 H



DIMMABLE



100
LPW
EFFICACY



3
YR
WARRANTY



80
CRI (Ra)



OMNI
DIRECTIONAL



LM 79

LM 80

TM 21



FILAMENT PRODUCT FEATURES



The GREEN CREATIVE Filament Series features a wide variety of vintage style bulbs that use the latest in LED technology. Each filament bulb uses a high quality LED package which results in longer lifetimes and higher efficacies. Each lamp's micro-designed driver provides excellent dimming performance without the need for a heat sink.

G25 4.5W FILAMENT DIM. TITANIUM LED SERIES



APPLICATIONS

Chandelier Lighting



General Lighting



Ambient Lighting



Ref.#: DS135-G25-F-4.5W-DIM

SPECIFICATIONS

| | |
|-----------------------------|-------------------------|
| Product Model | 57893 4.5FG25DIM/827 |
| Type | G25 |
| Base | E26 |
| Power (W) | 4.5 |
| Voltage - Frequency | 120V 60Hz |
| Color Temp. (ANSI) | Soft White 2700K |
| CRI (Ra) | 80 |
| Typical lumens (lm) | 450 |
| Efficacy (LPW) | 100 |
| Beam Angle | 330° |
| Dimmable | Yes** |
| Power Factor | 0.9 |
| Rated Lifetime - L70 (hrs.) | 15,000 |
| Dia. x MOL | 3.15"x4.65" (80x118mm) |
| Weight (lb. / g) | 0.11lb. / 50g |

* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 15,000-hr lifetime

** List of tested dimmer switches available on website

*** Suitable for damp locations. Not for use where directly exposed to weather or water