



6W REPLACES

13-18W CFL

60% Energy Savings

PRO




- ⌚ **HYBRid installation - DIRect or BYPass**
- ⌚ **Compatible with magnetic ballasts - DIRect installation**
- ⌚ **Built-in universal voltage driver - BYpass installation**
- ⌚ **Compatible with G24d, GX24d, G24q & GX24q bases**
- ⌚ **Exceptional efficacy 93 LPW**
- ⌚ **Lasts 4 times longer than CFL**




PL PRODUCT FEATURES

BYPass Installation - Electronic Ballasts

This PL H lamp is not compatible with electronic ballasts and requires bypassing the ballast during installation. The lamp runs directly off line voltage to eliminate compatibility problems, incidental power loss, lifetime issues, and maintenance costs associated with ballasts.



HYBRid Installation - DIRect or BYPass - Magnetic Ballasts



When used with a magnetic ballast, the PL H can function as a plug & play lamp and operate with the existing ballast. If the ballast is not compatible, it can be bypassed and the lamp can run directly off line voltage.

PL H 6W BYP TITANIUM LED SERIES

APPLICATIONS

Retail



Hospitality




Office



Ref.#: DS154-PLH-6W-BYP

- Base:** G24d, GX24d, G24q & GX24q (2/4-pin CFL)
- Voltage:** Magnetic ballast compatible
120-277V
- Dimmable:** No
- PF:** 0.9
- Lifetime:** 50,000 hrs
- Weight:** 0.15lb / 68g



SPECIFICATIONS*

Model	Product	Power (W)	CCT	CRI (typ.)	Lumens	LPW	Beam Angle
6PLH/835/BYP	57904	6	Neutral White 3500K	80	550	92	110°
6PLH/840/BYP	57905	6	Cool White 4000K	80	560	93	110°

* Specification data is preliminary and may be subject to change
 ** Suitable for damp locations. Not for use where directly exposed to weather or water
 *** Not intended for use in enclosed fixtures
 **** Full installation guide and more details available on website