

# B10 3.5W FILAMENT DIM. TITANIUM LED SERIES



## APPLICATIONS

### Chandelier Lighting



### General Lighting



### Ambient Lighting



Ref.#: DS201-B10-F-3.5W-DIM-250117

## SPECIFICATIONS

Product Model	58009 3.5FB10DIM/827/R
Type	B10
Base	E12
Power (W)	3.5
Voltage - Frequency	120V 60Hz
Color Temp. (ANSI)	Soft White 2700K
CRI (Ra)	82
Typical lumens (lm)	320
Efficacy (LPW)	91
Beam Angle	320°
Dimmable	Yes**
Power Factor	0.9
Rated Lifetime - L70 (hrs.)	15,000
Dia. x MOL	1.26"x3.62" (32x92mm)
Weight (lb. / g)	0.03lb. / 14g

\* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 15,000-hr lifetime

\*\* List of tested dimmer switches available on website

\*\*\* Suitable for damp locations. Not for use where directly exposed to weather or water