

# 5" OR 6" DL 11W WARM DIM. TITANIUM LED SERIES



## APPLICATIONS

### General Lighting



### Recessed Lighting



### Accent Lighting



## SPECIFICATIONS

Product Model	58100 11DL6DIM/8CCTD
Type	5" OR 6" DOWNLIGHT
Base	E26 (GU24 optional)
Power (W)	11
Voltage - Frequency	120V 60Hz
Color Temp. (ANSI)	Amber White-Soft White 2200K-2700K
CRI (Ra) (typ.)	82
Typical lumens (lm)	770
Efficacy (LPW)	70
Beam Angle	110°
Dimmable	Yes**
Power Factor	0.9
Rated Lifetime - L70 (hrs.)	40,000
Dia. x MOL	7.48"x3.00" (190x76mm)
Weight (lb. / g)	0.55lb / 249g

\* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$20 LED with 40,000-hr lifetime

\*\* List of tested dimmer switches available on website

\*\*\* Not intended for use in enclosed fixtures

\*\*\*\* Suitable for damp locations. Not for use where directly exposed to weather or water

Ref.:# DS178-DL-11W-WARM-DIM-150217