

## SPECIFICATIONS\*\*

Product Model	97750 14.5PLL/835/DIR
Type	PLL
Base	2G11
Power (W)	14.5
Voltage - Frequency	120-277V 50-60Hz
Color Temp. (ANSI)	Neutral White 3500K
CRI (Ra)	80
Typical lumens (lm)	1550
Efficacy (LPW)	107
Light Emitting Area	280°
Beam Angle	120°
Dimmable	Yes
Power Factor	0.9
THD	<20%
Rated Lifetime - L70 (hrs.)	50,000
Dia. x MOL	1.71"x16.54" (44x420mm)
Weight (lb. / g)	0.31lb. / 140g

Ref.# DS086-PLL-14.5W-DIR

## BALLAST PERFORMANCE

Bare Lamp (W)	System (W)	3500K Lumens
<b>14.5</b>	<b>19</b>	<b>1550</b>

\* Suitable for use in totally enclosed fixtures

\*\* Suitable for damp locations. Not for use where directly exposed to the weather or water