

# 5" OR 6" DOWNLIGHT 10W TITANIUM LED SERIES



## APPLICATIONS

### General Lighting



### Recessed Lighting



### Accent Lighting



Ref.#DS092-6DL-10W

## SPECIFICATIONS\*\*

| Product Model                      | 97756<br>10DL6DIM/827             | 97757<br>10DL6DIM/830             |
|------------------------------------|-----------------------------------|-----------------------------------|
| <b>Type</b>                        | 5" or 6" Downlight                | 5" or 6" Downlight                |
| <b>Base</b>                        | E26 / LED Adapter (GU24 optional) | E26 / LED Adapter (GU24 optional) |
| <b>Power (W)</b>                   | 10                                | 10                                |
| <b>Voltage - Frequency</b>         | 120V 60Hz                         | 120V 60Hz                         |
| <b>Color Temp. (ANSI)</b>          | Soft White 2700K                  | Warm White 3000K                  |
| <b>CRI (Ra)</b>                    | 80                                | 80                                |
| <b>Typical lumens (lm)</b>         | 700                               | 700                               |
| <b>Efficacy (LPW)</b>              | 65                                | 65                                |
| <b>Beam Angle</b>                  | 100°                              | 100°                              |
| <b>Dimmable</b>                    | Yes***                            | Yes***                            |
| <b>Housing Compatibility</b>       | Most 5" and 6" housing            | Most 5" and 6" housing            |
| <b>Power Factor</b>                | 0.9                               | 0.9                               |
| <b>Rated Lifetime - L70 (hrs.)</b> | 35,000                            | 35,000                            |
| <b>Dia. x MOL</b>                  | 7.48"x3.74" (190x95mm)            | 7.48"x3.74" (190x95mm)            |
| <b>Weight (lb. / g)</b>            | 0.71lb. / 322g                    | 0.71lb. / 322g                    |

\* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$4 incandescent with 1000-hr lifetime, \$28 LED with 35,000-hr lifetime  
 \*\* Specification data is preliminary and may be subject to change

\*\*\* List of tested dimmer switches available on website  
 \*\*\*\* Suitable for damp locations. Not for use where directly exposed to weather or water