

# A19 9W DIM. TITANIUM LED SERIES



## APPLICATIONS

### General Lighting



### Downlighting



### Uplighting



Ref.#:DS170-A19-9W

## SPECIFICATIONS

Product Model	97780 9A19DIM/827	97781 9A19DIM/830	97782 9A19DIM/840
Type	A19	A19	A19
Base	E26	E26	E26
Power (W)	9	9	9
Voltage - Frequency	120V 60Hz	120V 60Hz	120V 60Hz
Color Temp. (ANSI)	Soft White 2700K	Warm White 3000K	Cool White 4000K
CRI (Ra) (typ.)	82	82	82
Typical lumens (lm)	800	820	860
Efficacy (LPW)	89	91	96
Beam Angle	300°	300°	300°
Dimmable	Yes**	Yes**	Yes**
Power Factor	0.9	0.9	0.9
Rated Lifetime - L70 (hrs.)	25,000	25,000	25,000
Dia. x MOL	2.36"x4.41" (60x112mm)	2.36"x4.41" (60x112mm)	2.36"x4.41" (60x112mm)
Weight (lb. / g)	0.10lb. / 45g	0.10lb. / 45g	0.10lb. / 45g

\* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 25,000-hr lifetime

\*\* Suitable for use in totally enclosed fixtures

\*\*\* Suitable for damp locations. Not for use where directly exposed to weather or water