

2X4' 36W RETROFIT KIT TITANIUM LED SERIES



Preliminary Specifications

SPECIFICATIONS*

Product Model	97799 36TROFKIT24DIM/830/277V	97800 36TROFKIT24DIM/835/277V	97801 36TROFKIT24DIM/840/277V	97802 36TROFKIT24DIM/850/277V (MTO)
Type	2x4' Troffer Retrofit Kit	2x4' Troffer Retrofit Kit	2x4' Troffer Retrofit Kit	2x4' Troffer Retrofit Kit
Power (W)	36	36	36	36
Voltage - Frequency	120-277V 50-60Hz	120-277V 50-60Hz	120-277V 50-60Hz	120-277V 50-60Hz
Color Temp. (ANSI)	Warm White 3000K	Neutral White 3500K	Cool White 4000K	Daylight 5000K
CRI (Ra)	80	80	80	80
Typical lumens (lm)	3710	3850	3960	4070
Efficacy (LPW)	103	107	110	113
Beam Angle	120°	120°	120°	120°
Dimmable	Yes	Yes	Yes	Yes
Power Factor	0.9	0.9	0.9	0.9
THD	<20%	<20%	<20%	<20%
Rated Lifetime - L70 (hrs.)	50,000	50,000	50,000	50,000
Dia. x MOL	23.94"x46.65"(608x1185mm)	23.94"x46.65"(608x1185mm)	23.94"x46.65"(608x1185mm)	23.94"x46.65"(608x1185mm)
Weight (lb. / g)	11.51lb / 5.22kg	11.51lb / 5.22kg	11.51lb / 5.22kg	11.51lb / 5.22kg

* Specification data is preliminary and subject to change

** Not intended for use in totally enclosed fixtures

*** Suitable for damp locations. Not for use where directly exposed to the weather or water

Ref.:# DS111-TROFKIT-36W-2X4