

B11 5.5W DIM. TITANIUM LED SERIES

APPLICATIONS

Chandelier



Sconce



Uplighting



Ref.:# DS101-B11-5.5W

SPECIFICATIONS

Product Model	97823 5.5B11DIM/827	97824 5.5B11DIM/827/E26
Type	B11 (candle)	B11 (candle)
Base	E12	E26
Power (W)	5.5	5.5
Voltage - Frequency	120V 60Hz	120V 60Hz
Color Temp. (ANSI)	Warm White 2700K	Warm White 2700K
CRI (Ra)	80	80
Typical lumens (lm)	500	500
Efficacy (LPW)	91	91
Beam Angle	230°	230°
Dimmable	Yes**	Yes**
Power Factor	0.9	0.9
Rated Lifetime - L70 (hrs.)	25,000	25,000
Dia. x MOL	1.50"x4.21" (38x107mm)	1.50"x4.16" (38x106mm)
Weight (lb. / g)	0.11lb / 49g	0.12lb / 54g

* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 25,000-hr lifetime

** List of tested dimmer switches available on website

*** Not intended for use in totally enclosed fixtures

**** Suitable for damp locations. Not for use where directly exposed to weather or water