

# A19 9W DIM. GU24 TITANIUM LED SERIES



## APPLICATIONS

### General Lighting



### Downlighting



### Uplighting



Ref.#:DS232-A19-9W-GU24-070417

## SPECIFICATIONS

| Product Model               | 97908<br>9A19DIM/827/GU24 | 97909<br>9A19DIM/830/GU24 | 97910<br>9A19DIM/840/GU24 |
|-----------------------------|---------------------------|---------------------------|---------------------------|
| Type                        | A19                       | A19                       | A19                       |
| Base                        | GU24                      | GU24                      | GU24                      |
| Power (W)                   | 9                         | 9                         | 9                         |
| Voltage - Frequency         | 120V 60Hz                 | 120V 60Hz                 | 120V 60Hz                 |
| Color Temp. (ANSI)          | Soft White 2700K          | Warm White 3000K          | Cool White 4000K          |
| CRI (Ra) (typ.)             | 82                        | 82                        | 82                        |
| Typical lumens (lm)         | 800                       | 820                       | 860                       |
| Efficacy (LPW)              | 89                        | 91                        | 96                        |
| Beam Angle                  | 240°                      | 240°                      | 240°                      |
| Dimmable                    | Yes**                     | Yes**                     | Yes**                     |
| Power Factor                | 0.9                       | 0.9                       | 0.9                       |
| Rated Lifetime - L70 (hrs.) | 25,000                    | 25,000                    | 25,000                    |
| Dia. x MOL                  | 2.44"x4.45" (62x113mm)    | 2.44"x4.45" (62x113mm)    | 2.44"x4.45" (62x113mm)    |
| Weight (lb. / g)            | 0.25lb. / 113g            | 0.25lb. / 113g            | 0.25lb. / 113g            |

\* Savings per lamp based on \$0.11 / kw energy cost, 12 hrs / day lamp usage, \$2 incandescent with 1000-hr lifetime, \$16 LED with 25,000-hr lifetime

\*\* Suitable for use in totally enclosed fixtures

\*\*\* Suitable for damp locations. Not for use where directly exposed to weather or water