



CRIMP TOOL,MECHANICAL (K425BG)

Crimping Tool with D³ and BG die grooves

Cat No: 50020650

UPC No: 783310020653

Description

- Designed for crimping a wide range of overhead service entrance connections, overhead splices, and overhead taps
- Easy-to-use MD-6 type "pop" tool, K425 tools are equipped with D³ die groove and either "BG" or "O" die groove
- K425K tools are equipped with a die groove for Kearney "O" dies and either a 5/8 IN or "O" die groove
- The D³ die groove serves as a die seat for all Greenlee KD6 and industry "W" type dies
- Bent fiberglass handles provide a solid grip, good leverage and better durability than wood
- Low friction-impregnated bushings at pivot joints provide smooth operation and long life
- Complete crimps are assured with an over-center cam mechanism
- Tool can easily be checked visually for proper adjustment and can be adjusted with Allen wrenches

Specifications

- Application : For Crimping A Wide Range Of Overhead Service Entrance Connections, Overhead Splices, And Overhead Taps
- Crimping Force : 9000.000 LB (40.000 KN)
- Includes : D3 And BG Die Grooves
- Overall Length : 25-3/8 IN (645.000 MM)
- Type : Manual
- Weight : 7.100 LB (3.200 KG)