



CRIMPER (3/0-400)



Cat No: **K09-3GL** UPC No: **783310026303**

Specifications

- Application : For Larger Copper Connector Sizes All The Way To 400 KCMIL (MCM)
- Crimping Capacity : 3/0 AWG - 400 KCMIL (MCM) Copper
- Overall Length : 25.500 IN (650.000 MM)
- Replacement Part : 02913 Die Set
- Standard : C/US UL Listed
- Type : K Series
- Weight : 6.400 LB (2.900 KG)

Description

- Crimps the larger copper connector sizes all the way to 400 kcmil (MCM)
- Color-coded, hexagonal rotating dies