

LCS-144

Electrician's Metal Cutting Circular Saw

14.4v
Lithium-Ion

The Greenlee circular saw is designed primarily to cut metal—almost any metal. This includes conduit, strut, and threaded rod. Plus, the blade doesn't leave burrs, so chasing threads or filing the edges isn't needed. The full surround blade guard contains most of the chips, and with its compact size, it will work where larger saws can't. It even has a LED work light so you can make straight cuts in dark locations.

- 1 High capacity battery: 14.4V LI-ION
- 2 Rotating speed: 3,600 rpm
- 3 Blade size: Outer diameter 5-3/8"
Arbor size: 20mm
- 4 Adjustable cutting depth up to 1-13/16"
- 5 Electric brake stops the blade instantaneously
- 6 Charging time (using LBC-81B charger):
Usable: 35 minutes • Full: 50 minutes
- 7 3-way chip control system (vacuum cleaner, chip case or eject from rear of tool)
- 8 Shaft lock for easy blade replacement
- 9 Electronic performance monitoring system maximizes battery life
- 10 LED work light



INCLUDES:

- (1) 14.4V Metal Cutting Circular Saw with LCS-M13C Metal Blade,
- (2) 14.4V Lithium-Ion Compact Batteries, (1) 14.4V – 28.8V Battery Charger,
- (1) Carrying Case

Also Available



LCS-W13A
CARBIDE-TIPPED
WOOD CIRCULAR
SAW BLADE - 5-3/8"
(REGULAR)



LCS-W13B
CARBIDE-TIPPED
WOOD CIRCULAR
SAW BLADE - 5-3/8"
(THIN)



LCS-M13C
CARBIDE-TIPPED
METAL CIRCULAR
SAW BLADE - 5-3/8"
(REGULAR)



LCS-M13D
CARBIDE-TIPPED
METAL CIRCULAR
SAW BLADE - 5-3/8"
(THIN)



No burrs!
Save time on the
jobsite with burr-
free cutting.