

T-Basket-Type Pulling Grips



- Use to pull in: conduit or tray.
- Type of pulls: medium-duty.
- Type of grip: double weave galvanized steel mesh with flexible pulling eye.
- Select the grip with a maximum rated capacity that meets or exceeds the cable puller's maximum pulling force.

| CAT. NO. | UPC NO. | CABLE DIAMETER RANGE | | MAXIMUM RATED CAPACITY | | EYE LENGTH | | MESH LENGTH | | |
|-----------------|---------|----------------------|--------------|------------------------|------|------------|-------|-------------|-------|--|
| | | INCH | mm | LBS. | kN | INCH | mm | INCH | mm | |
| SHORT | | | | | | | | | | |
| 30558 | 30558 | .50 - .61 | 12.7 - 15.5 | 900 | 4 | 8 | 203.2 | 21 | 533.4 | |
| 30560 | 30560 | .62 - .74 | 15.6 - 18.9 | 1120 | 4.9 | 8 | 203.2 | 24 | 610 | |
| 30562 | 30562 | .75 - .99 | 19.0 - 25.3 | 1360 | 6 | 9 | 228.6 | 24 | 610 | |
| 30564 | 30564 | 1.00 - 1.49 | 25.4 - 38.0 | 1920 | 8.7 | 9 | 228.6 | 24 | 610 | |
| 30566 | 30566 | 1.50 - 1.99 | 38.1 - 50.7 | 3280 | 14.5 | 11 | 279.4 | 24 | 610 | |
| 30568 | 30568 | 2.00 - 2.49 | 50.8 - 63.3 | 3700 | 16.4 | 12 | 304.8 | 24 | 610 | |
| 30570 | 30570 | 2.50 - 2.99 | 63.5 - 76.1 | 4900 | 21.7 | 12 | 304.8 | 24 | 610 | |
| 30572 | 30572 | 3.00 - 3.49 | 76.2 - 88.8 | 4900 | 21.7 | 14 | 355.6 | 24 | 610 | |
| 30574 | 30574 | 3.50 - 3.99 | 88.9 - 101.3 | 6200 | 27.5 | 14 | 355.6 | 26 | 660.4 | |
| STANDARD | | | | | | | | | | |
| 30576 | 30576 | .75 - .99 | 19.0 - 25.3 | 1360 | 6 | 9 | 228.6 | 36 | 914.4 | |
| 30578 | 30578 | 1.00 - 1.49 | 25.4 - 38.0 | 1920 | 8.7 | 9 | 228.6 | 36 | 914.4 | |
| 31010 | 31010 | 1.50 - 1.99 | 38.1 - 50.7 | 3280 | 14.5 | 11 | 279.4 | 36 | 914.4 | |
| 30580 | 30580 | 2.00 - 2.49 | 50.8 - 63.3 | 3700 | 16.4 | 12 | 304.8 | 36 | 914.4 | |
| 31012 | 31012 | 2.50 - 2.99 | 63.5 - 76.1 | 4900 | 21.7 | 12 | 304.8 | 36 | 914.4 | |
| 30582 | 30582 | 3.00 - 3.49 | 76.2 - 88.8 | 4900 | 21.7 | 14 | 355.6 | 36 | 914.4 | |
| 31014 | 31014 | 3.50 - 3.99 | 88.9 - 101.3 | 6200 | 27.5 | 14 | 355.6 | 40 | 1016 | |

K Basket-Type Pulling Grips



- Use to pull in: conduit or tray.
- Type of pulls: heavy-duty, long, hard runs.
- Type of grip: double-weave galvanized steel mesh with forged steel swivel eye.
- Select the grip with a maximum rated capacity that meets or exceeds the cable puller's maximum pulling force.

| CAT. NO. | UPC NO. | CABLE DIAMETER RANGE | | MAXIMUM RATED CAPACITY | | EYE LENGTH | | MESH LENGTH | | ROTATING EYE DIA. | |
|-----------------|---------|----------------------|---------------|------------------------|------|------------|-------|-------------|--------|-------------------|------|
| | | INCH | mm | LBS. | kN | INCH | mm | INCH | mm | INCH | mm |
| STANDARD | | | | | | | | | | | |
| 30442 | 30442 | .50 - .61 | 12.7 - 15.5 | 1120 | 4.9 | 5 | 127 | 16 | 406.4 | 7/8 | 22.2 |
| 30998 | 30998 | .62 - .74 | 15.6 - 18.9 | 1360 | 6 | 5 | 127 | 16 | 406.4 | 7/8 | 22.2 |
| 30460 | 30460 | .75 - .99 | 19.0 - 25.3 | 1920 | 8.5 | 6 | 152.4 | 32 | 812.8 | 1 | 25.4 |
| 31000 | 31000 | 1.00 - 1.49 | 25.4 - 38.0 | 3280 | 14.5 | 7 | 177.8 | 33 | 838.2 | 1-3/8 | 34.9 |
| 30462 | 30462 | 1.50 - 1.99 | 38.1 - 50.7 | 3280 | 14.5 | 7 | 177.8 | 34 | 863.6 | 1-3/8 | 34.9 |
| 31002 | 31002 | 2.00 - 2.49 | 50.8 - 63.3 | 5440 | 24.1 | 9 | 228.6 | 36 | 914.4 | 1-5/8 | 41.2 |
| 30464 | 30464 | 2.50 - 2.99 | 63.5 - 76.1 | 6600 | 29.3 | 10 | 254 | 38 | 965.2 | 1-7/8 | 47.6 |
| 31004 | 31004 | 3.00 - 3.49 | 76.2 - 88.8 | 8200 | 36.5 | 10 | 254 | 39 | 990.6 | 1-7/8 | 47.6 |
| 30466 | 30466 | 3.50 - 3.99 | 88.9 - 101.5 | 9600 | 42.7 | 10 | 254 | 41 | 1041.4 | 1-7/8 | 47.6 |
| 31006 | 31006 | 4.00 - 4.49 | 101.6 - 114.2 | 9600 | 42.7 | 10 | 254 | 42 | 1066.8 | 1-7/8 | 47.6 |
| 30468 | 30468 | 4.50 - 4.99 | 114.3 - 126 | 9600 | 42.7 | 10 | 254 | 58 | 1473.2 | 1-7/8 | 47.6 |
| 30470 | 30470 | 5.00 - 5.99 | 127 - 152.3 | 9600 | 42.7 | 10 | 254 | 60 | 1524 | 1-7/8 | 47.6 |

NOTE: Rope is a very critical link in the cable pulling system. See page 166 for proper pulling rope selection.