



Dependable Power for Any Application

Product Datasheet

575Δ Primary Volts - 230Y/133 Secondary Volts - 3Ø Drive Isolation Transformer - Three Phase

Catalog #: DTHA0202S



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Aluminum foil windings
- Copper wire terminations
- Wound/Distributed core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900
- Optional wall mounting kit - part # PL79911

BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	20.00
Primary Voltage:	575Δ
Secondary Voltage:	230Y/133
Frequency:	60 Hz
ANFC Taps:	1
BNFC Taps:	1
Taps % Steps:	5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	20.77 (52.8)
Width (In./cm):	20.94 (53.2)
Depth (In./cm):	10.18 (25.9)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Floor
Wiring Diagram:	62

PACKAGING

Ship Weight (Lbs/Kg):	435 (197.0)
-----------------------	-------------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf