

Search > Results for 108216 > MH400/U/ED28 108216 400W MH ED28 MOG PRLUME



MH400/U/ED28 108216 400W MH ED28 MOG PRLUME

Product Number: 108216
UPC: 807154182161

[Log In for Price and Availability](#)

Specifications	Resources	Technical
ANSI Code 1	M59/E	
Applications	Municipal lighting, Retail, Security lights, Street lighting	
Average Life (Hrs)	15000	
Base	Mogul	
Brand	ProLume	
Bulb	ED28	
CRI	65	
Color Temperature	4000	
Design Lumens	23000	
Dimmable	Yes	
HTS code	8539320040	
Initial Lumens	39000	
Inner Carton Quantity	1	
Input Frequency (Hz)	60	
KR85 Content	<120	
Lens	Clear	
Markets	Residential, Commercial	
Master Carton Quantity	12	
Maximum Overall Diameter	3.54	
Maximum Overall Length	8.25	
Nominal Length	8.25	
Operating Position	Universal	
Product Category	Metal Halide	
Product Description	400W MH ED28 MOG PRLUME	
Product Number	108216	
Start Type	Probe Start	
UN2911	No	
Wattage (W)	400	

Substitute Items:



MH400U/ED28/M 64488/SYL 400W MH ED28 MO