

Search > Results for 108254 > MH100/U/MED/PS 108254 100W MH ED17 MED PS PROLUME \*\*\*UN2911\*\*\*



# MH100/U/MED/PS 108254 100W MH ED17 MED PS PROLUME \*\*\*UN2911\*\*\*

Product Number: 108254  
UPC: 807154182541

[Log In for Price and Availability](#)

Specifications	Resources	Technical
ANSI Code 1	M90/E	
Applications	Roadway, Parking lot, retail, security, street, wall wash	
Average Life (Hrs)	15000	
Base	Medium	
Brand	ProLume	
Bulb	ED17	
CRI	65	
Color Temperature	4000	
Design Lumens	5900	
Dimmable	Yes	
HTS code	8539320040	
Initial Lumens	9100	
Inner Carton Quantity	1	
Input Frequency (Hz)	60	
KR85 Content	<120	
Lens	Clear	
Markets	Residential, Commercial	
Master Carton Quantity	12	
Maximum Overall Diameter	2.13	
Maximum Overall Length	5.45	
Nominal Length	5.45	
Operating Position	Universal	
Product Category	Metal Halide	
Product Description	100W MH ED17 MED PS PROLUME ***UN29	
Product Number	108254	
Start Type	Pulse Start	
UN2911	Yes	
Wattage (W)	100	

### Products



#### Lamps



#### Ballasts



#### Luminaires



### Resources

[Catalog](#)

[ProLED Brochure](#)

[New Products \(PDF\)](#)

[New Products \(XLS\)](#)

[ProLED Panel Light](#)

[ProLED Volumetric](#)

[ProLED Downlight](#)

[Retrofit](#)

### Contact Us

**Corporate Office:**  
Halco Lighting Technology  
2940 Pacific Drive  
Norcross, GA 30071  
Toll Free: 800.677.3334  
Office: 770.242.3612  
Fax: 800.880.0822  
Email: [customer@halco.com](mailto:customer@halco.com)