

Search > Results for 108294 > MP400/BU 108294 400W MP ED37 EX39 BU PROLUME



# MP400/BU 108294 400W MP ED37 EX39 BU PROLUME

Product Number: 108294  
UPC: 807154182947

[Log In for Price and Availability](#)

Specifications	Resources	Technical
ANSI Code 1	M59/O	
Applications	Municipal lighting, Retail, Security lights, Street lighting	
Average Life (Hrs)	15000	
Base	EX39	
Brand	ProLume	
Bulb	ED37	
CRI	65	
Color Temperature	4000	
Design Lumens	22000	
Dimmable	Yes	
HTS code	8539320040	
Initial Lumens	37000	
Inner Carton Quantity	1	
Input Frequency (Hz)	60	
KR85 Content	<120	
Lens	Clear	
Markets	Residential, Commercial	
Master Carton Quantity	6	
Maximum Overall Diameter	4.62	
Maximum Overall Length	11.5	
Nominal Length	11.5	
Operating Position	Base Up	
Product Category	Metal Halide	
Product Description	400W MP ED37 EX39 BU PROLUME	
Product Number	108294	
Start Type	Probe Start	
UN2911	No	
Wattage (W)	400	

### Products



#### Lamps



#### Ballasts



#### Luminaires



### Resources

[Catalog](#)

[ProLED Brochure](#)

[New Products \(PDF\)](#)

[New Products \(XLS\)](#)

[ProLED Panel Light](#)

[ProLED Volumetric](#)

[ProLED Downlight](#)

[Retrofit](#)

### Contact Us

**Corporate Office:**  
Halco Lighting Technology  
2940 Pacific Drive  
Norcross, GA 30071  
Toll Free: 800.677.3334  
Office: 770.242.3612  
Fax: 800.880.0822  
Email: [customer care@halco.com](mailto:customer care@halco.com)