

Search > Results for 60501 > MP750/BU/PS 60501 750W MP BT37 EX39 BU PS PROLUME ***UN2911***






**MP750/BU/PS 60501
750W MP BT37 EX39 BU
PS PROLUME
UN2911**




Product Number: 60501
UPC: 807154605019

[Log In for Price and Availability](#)

Specifications	Resources	Technical
ANSI Code 1	M149/O	
Applications	Municipal lighting, Retail, Security lights, Street lighting	
Average Life (Hrs)	15000	
Base	EX39	
Brand	ProLume	
Bulb	ED37	
CRI	65	
Color Temperature	4000	
Design Lumens	55000	
Dimmable	Yes	
HTS code	8539320040	
Initial Lumens	75000	
Inner Carton Quantity	1	
Input Frequency (Hz)	60	
KR85 Content	<120	
Lens	Clear	
Markets	Residential, Commercial	
Master Carton Quantity	6	
Maximum Overall Diameter	4.62	
Maximum Overall Length	11.5	
Nominal Length	11.5	
Operating Position	Base Up	
Product Category	Metal Halide	
Product Description	750W MP BT37 EX39 BU PS PROLUME ***	
Product Number	60501	
Start Type	Pulse Start	
UN2911	Yes	
Wattage (W)	750	


Products






Resources


Lamps



Ballasts



Luminaires



Catalog
ProLED Brochure
New Products (PDF)
New Products (XLS)

Contact Us

ProLED Panel Light
ProLED Volumetric
ProLED Downlight Retrofit

Corporate Office:
Halco Lighting Technology
2940 Pacific Drive
Norcross, GA 30071
Toll Free: 800.677.3334
Office: 770.242.3612
Fax: 800.880.0822
Email: customer care@halco.com

[Top](#)



Lamps ▾

Ballasts ▾

Luminaires ▾

Company ▾

Customer Care ▾

Contact Us

