



Bulb	Base	Product Number	Product Code	Description	Inner/Master	Volts	Lumens	Avg. Life	Design Filament	MOL	Beam Spread
75 WATT (cont'd)											
PAR30	Med.	355149	HP30SP75/SG (E)	Spot Long Neck	15	130	940	2000	CC-8	4½	16
		229344	HP30SP75L/M (E)	Spot Long Neck	15	120	940	2000	CC-8	4½	16
		816393	HP30WFL75L/M (E)	Wide Flood Long Neck	6	120	1050	2000	CC-8	4¾	60
PAR38	Med.	107576	HP38FL75 (E)	Flood Prism®	15	130	950	2500	CC-8	5¾	30
		133124	HP38FL75/M (E)	Flood	12	120	1030	2500	CC-8	5⅝	25
R20	Med.	9105	R20FL75	Flood Halco®	10/100	130	580	3000	C-9	3¾	-
R30	Med.	104120	R30BLB75	Blacklight Blue Halco®	12/24	120	-	2000	C-9	5¾	-
		104082	R30GRO75	Plant Grow Halco®	12/24	120	560	2000	C-9	5¼	-
		104017	R30FL75/ND	FL Neodymium PureLite®	6/24	120	500	5000	CC-6	5⅝	-
T10	Med.	817754	75T10/45	Clear Showcase Major	24	120	800	1000	C-23	11¾	-
85 WATT											
BR30	Med.	104075	BR30FL85	Flood Halco®	24	130	780	5000	C-9	5¼	-
BR40	Med.	404080	BR40FL85/P5	Flood Prism® Long Life	24	130	720	5000	C-9M	6¾	-
90 WATT											
A19	Med.	288571	A19FR90/10	Frost Krypton SG	2/120	130	800	10000	C-9	4⅞	-
		382671	A19TS90	Traffic Signal SG	2/120	125	1040	8000	C11-V	4¾	-
TB19	Med.	816745	TB19FR90	Frost Halogen Major	1/60	120	1580	2000	CC-8	4⅞	-
PAR38	Med.	107644	HP38FL90 (E)	Flood Prism®	15	130	1220	2500	CC-8	5¾	30
		107696	HP38FL90/120 (E)	Flood Prism®	15	120	1220	2500	CC-8	5¾	30
		265629	HP38FL90/M (E)	Flood	12	120	1280	2000	CC-8	5⅝	28
		266007	HP38FL90/M130 (E)	Flood	12	130	1280	2000	CC-8	5⅝	28
		261776	HP38FL90/SG (E)	Flood	12	130	1280	2500	CC-8	5⅝	28
		107840	HP38FL90/FR (E)	Frost Flood Prism®	15	120	1150	2500	CC-8	5¾	30
		107584	HP38SP90 (E)	Spot Prism®	15	130	1220	2500	CC-8	5¾	10
		265595	HP38SP90/M (E)	Spot	12	120	1280	2000	CC-8	5⅝	12
		261784	HP38SP90/SG (E)	Spot	12	130	1280	2500	CC-8	5⅝	12
100 WATT											
A19	Med.	6227	A19CL100/1	Clear Halco®	120	120	1150	1500	CC-6	4¼	-
		6327	A19CL100/5	Clear Halco®	120	130	950	5000	C-9	4¼	-
		103516	A19CL100/P5	Clear Prism® Long Life	120	130	1050	5000	C-9M	4¼	-
		103014	A19CL100/P10	CL Prism® Ultra Life®	20/120	120	870	10000	C-9M	4¼	-
		101182	A19CL100/SB	Clear Silver Bowl	12/120	130	830	5000	C-9	4¼	-
		374744	A19FR100	Frost Major	48	120	1600	750	CC-6	4⅞	-
		6323	A19FR100/5	Frost Halco®	120	130	950	5000	C-9	4¼	-
		103566	A19FR100/P5	Frost Prism® Long Life	120	130	1050	5000	C-9M	4¼	-
		103028	A19FR100/P10	Frost Prism® Ultra Life®	20/120	120	870	10000	C-9M	4¼	-

To save energy costs, find the bulbs with the light output you need, then choose the one with the lowest watts.

(E) Means this lamp meets Federal Minimum Efficiency standards.