

Search > Results for 80860 > MR16FL5/830/GU10/LED 80860 LED MR16 5W 3000K DIMMABLE 40 DEGREE GU10 ProLED



**MR16FL5/830/GU10/LED
80860 LED MR16 5W
3000K DIMMABLE 40
DEGREE GU10 ProLED**

Product Number: 80860
UPC: 807154808601

[Log In for Price and Availability](#)

Specifications	Resources	Technical
Applications	Accent; Display; Retail,Education; Healthcare; Hospitality; office	
Average Life (Hrs)	40000	
Base	GU10	
Beam Angle	Flood	
Beam Spread	40	
Brand	ProLED	
Bulb	MR16	
CBCP	480	
CRI	82	
Color Temperature	3000	
Dimmable	Yes	
ENERGY STAR	No	
Equivalent Wattage	35	
HTS code	8543707000	
Initial Lumens	370	
Inner Carton Quantity	10	
Input Frequency (Hz)	60	
Markets	Residential, Commercial	
Master Carton Quantity	100	
Maximum Overall Diameter	2	
Maximum Overall Length	2.17	
Nominal Length	2.17	
Operating Position	Universal	
Product Category	LED	
Product Description	5W 3000K DIMMABLE 40 DEGREE GU10 ProLED	
Product Number	80860	
Voltage (V)	120	
Warranty (Yrs)	5	
Wattage (W)	5	

Substitute Items:



MR16FL4/830/GU10/LED 80819 LED MR16 4W 3000K DIMMABLE 40 DEGREE GU10 ProLED



MR16FL4/830/GU10/LED 80887 LED MR16 4.5W 3000K DIMMABLE 40 DEGREE GU10 ProLED