



Actual

**Catalog Number:** WR259  
**Product ID:** 7TAA267110R0010  
**UPC Number:** 78378610004  
**Status:** Active

Aluminum Wide Range H-Type Compression Connector Main: 1/0 - 2 ACSR, 2/0 - 1 Str., Tap: 1/0 - 2 ACSR, 2/0 - 2 Str., Die: D, D3

### North American Specifications (UNSPSC)

|                          |   |
|--------------------------|---|
| UNSPSC                   | 39121409 Wire connectors  |
| IGCC                     | 4543 Wire connectors  |
| Brand Name               | Blackburn   |
| Type                     | Wide-Range Tap Connector  |
| Special Features         | Made of 1350 Aluminum Alloy for high strength and high conductivity. Standard Compression tools and dies install all sizes - no special tools needed. Field-proven ribbed design enables excellent connector/conductor contact without distorting the conductor's shape. Fold-in tabs provide tab interlock as tool closes. Prefilled with oxide inhibitor held captive in the rib/connection area. |
| Application              | For Combinations of Aluminum to Aluminum and Aluminum to Copper Conductors.   |
| Standard                 | RUS Accepted. Complies with ANSI C119.4 Specifications  |
| Size                     | Length 1-7/8 inch   |
| Connection               | Compression/ Crimp  |
| Wire Size                | Main: 1/0 - 2 ACSR, 2/0 - 1 Stranded, Tap: 1/0 - 2 ACSR, 2/0 - 2 Stranded   |
| Number Of Conductors     | 2   |
| Material                 | Aluminum  |
| Voltage Rating           | None since Uninsulated  |
| Insulation               | None  |
| Temperature Rating       | up to 90 Degrees C.   |
| Mounting                 | None  |
| Environmental Conditions | All Seasons / Conditions  |

### Packaging

|                           |                 |
|---------------------------|-----------------|
| Inner Quantity            | 25              |
| Outer Quantity            | 250             |
| Outer Dimensions (inches) | 14.1x13.7x11.4  |
| Weight Uom                | 19 lbs. per 100 |

### Documents / Support Tools

|                         |                      |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)