

## Fluorescent Light Kit & Accessories *FLK Series*



### Features

- Light kits are offered in 18", 24" and 48" widths.
- CSA and UL component recognized.
- Operating voltage 115 AC 60Hz
- 115V AC, features a manually operated switch, 115V convenience outlet, durable plastic lens, and 6 foot power cord (without plug).
- Can mount into light mounting channel, bolt through enclosure or by using magnet strip (available separately - see chart below.)
- 1¾" high x 4½" deep.
- Finished in white.
- Use standard 18", 24" or 48" T8 fluorescent bulb (not included)
- Magnet mount
  - Can be used with mild steel enclosures only.



### Accessories

#### Remote Door Switches

Part No.	Description
FLK18T8 <sup>1</sup>	18" Fluorescent Light Kit 115V
FLK24T8 <sup>1</sup>	24" Fluorescent Light Kit 115V
FLK48T8 <sup>1</sup>	48" Fluorescent Light Kit 115V
FLK18MM	Magnet mount for 18" and 24" kit
FLK48MM	Magnet mount for 48" light kit

<sup>1</sup> T8 fluorescent bulb not included

*Data subject to change without notice.*