

EVO 7 Mechanical Hand Tool, Standard hand span 3.5" (90 mm), can be used with all variations of HellermannTyton's 18-80 lb. cable ties.

Article Number: 110-70083

Part Number: 110-70083

Type: EVO7



Type	EVO7
Color	Black (BK)
Features	<p>TLC Technology Patent-pending Tension/Lock/Cut Technology (TLC) technology delivers a "true" flush cut for a safer installation with no protrusions to damage neighboring components. The advanced operating system of the TLC technology provides operational reliability and durability resulting in fewer repairs and an extended lifespan; eases wear and tear on tool components.</p> <p>Ergonomics Contoured soft trigger and air-cushion handle keeps the wrist in an upright, neutral position providing greater operator control; minimizes slippage.</p> <p>Lightweight tool with the most technologically-advanced ergonomic design for reducing work-related risks such as fatigue and injury that effect productivity.</p> <p>Available in two trigger spans, Standard 3.5" (90 mm) and Short 3.1" (80 mm), to accommodate different hand sizes for better operator command with less force and fatigue.</p> <p>Tension Adjustment System Operating function offers 33 precise pre-set, easy-to-read settings (with 1/4" increments) that reduce subjectivity or the need for fine tuning.</p>
Cable Ties	Can be used with all variations of HellermannTyton's 18-80 lb. cable ties.
EAN code	4031026438535
Material Specification	RoHS
Tension Setting Tools	Adjustable
Tool property ETIM	Manual clipping
Tool Suitable cable tie material	Plastic
Typical Application	EVO 7 delivers precise tensioning and cut-off of HellermannTyton cable ties while reducing work related risks to quality, productivity and employee safety. For use in OEM applications (ie; Truck and Heavy Equipment, White Goods, Automotive), wire harness assembly and control panel building.