

MBT14S-S

Stainless Steel Tie, 150lb Length 14.3" Max Bun Dia 4" SS304, Metal, 100/pk

Article Number: 111-93148

Part Number: MBT14S-S

Type: MBT14SS

Material: SS304



1. Base Data

Part No. MBT14S-S

Type MBT14SS

Color Metal


Features HellermannTyton's stainless steel ties are designed to secure hoses, cables, poles, pipes, and more when harsh environmental conditions may adversely affect the bundling application. Used where corrosion, vibration, weathering, radiation, and temperature

Application

304 Material Grade 304 material is commonly used for stainless steel bundling applications and suits most general purpose requirements. It features the ability to withstand most environmental conditions, particularly in applications where vib

Label E-Number Finland	13 703 14
-------------------------------	-----------

2. Product Dimensions



Min. Tensile Strength	150 lbs / 670 N
------------------------------	-----------------

Length (L)	14.3 " / 362 mm
-------------------	-----------------

Width (W)	.18 " / 4.6 mm
------------------	----------------

Min. Ø Bundle	.59 " / 15.0 mm
----------------------	-----------------

Max. Ø Bundle	4 " / 102 mm
----------------------	--------------

4. Material and Specifications

Material	Stainless Steel Type SS304 (SS304)
-----------------	------------------------------------

Material Shortcut	SS304
--------------------------	-------

Operating Temperature	-112 °F to +1000 °F (-80 °C to +538 °C)
------------------------------	---

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100
Carton Qty.	1 Pieces
EAN code	5022660157509
UPC	08930620318

Stainless Steel Cable Ties

HellermannTyton's stainless steel ties are designed to secure hoses, cables, poles, pipes, and more when harsh environmental conditions may adversely affect the bundling application. Used where corrosion, vibration, weathering, radiation, and temperature extremes are a concern, HellermannTyton's stainless steel ties can be used in virtually any indoor, outdoor, and underground application.

MK9SST Stainless Steel Cable Tie Installation Tool

Product Selection					
Article No.	Part No.	Type	Description	Cable Tie Series	Pkg. Qty.
110-95000	MK9SST	MK9SST	Adapted for use with stainless steel ties, the MK9 Stainless Steel tool retains the same design features as the MK9 series. The MK9SST accommodates all HellermannTyton stainless steel ties. Comes standard with padded foam grips for comfort and control and a hook for hanging on a belt or tether.	All MBT Series for both 304 and 316 materials	1


304 Material

Grade 304 material is commonly used for stainless steel bundling applications and suits most general purpose requirements. It features the ability to withstand most environmental conditions, particularly in applications where vibration, general weathering, radiation and temperature extremes are a concern.

- Self locking, ball bearing mechanism for quick and easy installation, either by hand or by tensioning tool
- Fully enclosed head does not allow dirt or grit to interfere with locking mechanism
- High tensile strength option for added strength and safety on heavy duty applications



HellermannTyton's MK9SST tool is durable and lightweight, offering superior stainless steel cable tie installation.



Material Data	
Material	Stainless Steel Type SS304 (SS304)
Operating Temperature	-112 °F to +1000 °F (-80 °C to +538 °C)



Product Selection											
Article No.	Part No.	Type	Min. Tensile Strength		Length (L)		Max. Ø Bundle		Width (W)		
			lbs.	(N)	in.	(mm)	in.	(mm)	in.	(mm)	Pkg. Qty.
150 lb. Stainless Steel Ties											
111-93058	MBT5S-S	MBT5SS	150 lbs	(670)	5.0"	(127)	1"	(25)	.18"	(4.6)	100
111-93088	MBT8S-S	MBT8SS	150 lbs	(670)	7.9"	(201)	2"	(50)	.18"	(4.6)	100
111-93148	MBT14S-S	MBT14SS	150 lbs	(670)	14.3"	(362)	4"	(102)	.18"	(4.6)	100
111-93208	MBT20S-S	MBT20SS	150 lbs	(670)	20.5"	(521)	6"	(152)	.18"	(4.6)	100
111-93278	MBT27S-S	MBT27SS	150 lbs	(670)	26.8"	(681)	8"	(203)	.18"	(4.6)	100
111-93338	MBT33S-S	MBT33SS	150 lbs	(670)	33"	(838)	10"	(254)	.18"	(4.6)	100
250 lb. Stainless Steel Ties											
111-94088	MBT8H-S	MBT8HS	250 lbs	(1115)	7.9"	(201)	2"	(50)	.31"	(7.9)	50
111-94148	MBT14H-S	MBT14HS	250 lbs	(1115)	14.3"	(362)	4"	(102)	.31"	(7.9)	50
111-94208	MBT20H-S	MBT20HS	250 lbs	(1115)	20.5"	(521)	6"	(152)	.31"	(7.9)	50
111-94278	MBT27H-S	MBT27HS	250 lbs	(1115)	26.8"	(681)	8"	(203)	.31"	(7.9)	50
111-94338	MBT33H-S	MBT33HS	250 lbs	(1115)	33"	(838)	10"	(254)	.31"	(7.9)	50

Installation tools for the above cable ties - MK9SST. Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes. Stainless steel ties and materials should be tested thoroughly under end use conditions to determine suitability for the application.