

- ▶ Cable Ties
- ▼ Cable Ties with Fasteners
 - ▶ Arrowhead Push Mount Ties
 - ▶ Button Head Cable Ties
 - ▶ Edge Clip Cable Ties**
 - ▶ Fir Tree Mount Cable Ties
 - ▶ Screw Mount Cable Ties
 - ▶ Stud Mount Cable Ties
- ▶ Cable Tie Tools
- ▶ Clamps and Clips
 - ▶ Heatshrink Moulded Shapes
- ▶ Mounts
 - ▶ Heavy Duty Mounts
- ▶ Wire Connectors
- ▶ Wiring Duct
- ▶ Wiring Protection
- ▶ Labels, Printers and Software
 - ▶ Pre-Terminated Networking
- ▶ Copper Network Solutions
- ▶ Fiber Network Solutions
- ▶ Jacks and Wall Plates
- ▶ Residential Solutions
- ▶ Racks - Cable Management
- ▶ Surface Raceway Systems

156-00635

Cable Tie and Edge Clip, 50lb, 8.0" Long, EC4A, Panel Thickness .04"-12", PA66UV, Black, 100/bag

Article Number: 156-00635
 Part Number: 156-00635
 Type: T50REC4A



- Find a Distributor
- Order Samples
- Get Technical Drawings
- | → Share

Miscellaneous

Material	Polyamide 6.6 UV-resistant (PA66UV)
Part No.	156-00635
Type	T50REC4A
Color	Black (BK)
Features	<ul style="list-style-type: none"> • Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments. • Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
Min. Tensile Strength	50.0lbs / 225N
Length (L)	8.0" / 200mm
Length (L2)	0.55" / 14.0mm
Packaging Type	bag
Pkg. Qty.	100
Cable Tie	Polyamide 6.6 UV-stabilized (PA66UV)
EAN code	4031026405049
Edge Clip	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
Flammability	UL94 HB
Identification Plate Position	none
Material Specification	RoHS
Releasable Closure (Yes/No)	No
ROHS Conformity	<input checked="" type="checkbox"/> RoHS
Typical Application	The UV stabilized tie and edge clip assemblies are ideal for use where holes are not available or where adhesives are not strong enough. Edge clips are widely used for fixing and bundling cables and wires in the automotive, harness making, panel building and renewable energy industry.
Width (W)	0.18" / 4.6mm
Width (W2)	0.45" / 11.5mm
Height (H)	0.05" / 1.2mm
Height (H2)	0.43" / 10.8mm
Min. Å Bundle	0.06" / 4.0mm
Max. Å Bundle	2.0" / 45.0mm
Max. Panel Thickness	0.12" / 3.0mm
Min. Panel Thickness	0.04" / 1.0mm
Thickness	1.2mm

[Home](#) | [About HellermannTyton](#) | [Products](#) | [Careers](#) | [Contact](#) | [Terms](#)

© HellermannTyton North America 2011 | [TS16949, ISO 9001 and ISO 14001 Certified](#)

7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512