

- ▶ Cable Ties
- ▶ Cable Ties with Fasteners
- ▶ Cable Tie Tools
- ▶ Clamps and Clips
- ▶ Heatshrink Moulded Shapes
- ▼ Mounts
 - Adhesive Fastened Bases
 - Screw Fastened Bases**
 - Mounting Plates
 - Screw Mount
 - Push Mount
 - Masonry Mounts
 - Bundle Separator-Spacer
 - Grip Tie Mounts
- ▶ Heavy Duty Mounts
- ▶ Wire Connectors
- ▶ Wiring Duct
- ▶ Wiring Protection
- ▶ Labels, Printers and Software
- ▶ Pre-Terminated Networking
- ▶ Copper Network Solutions
- ▶ Fiber Network Solutions
- ▶ Jacks and Wall Plates
- ▶ Residential Solutions
- ▶ Racks - Cable Management
- ▶ Surface Raceway Systems

MB410C2

Cable Tie Mount - 4 Way Screw Mount 1.12"X1.12" - PA66, WH, T18-T50 Cable Ties, #8 Screw, 100/pk

Article Number: 151-28802
 Part Number: MB410C2
 Type: MB4



- Find a Distributor
- Order Samples
- Get Technical Drawings
- | → Share

Miscellaneous

Material	Polyamide 6.6 (PA66)
Part No.	MB410C2
Type	MB4
Color	White (WH)
Features	This HellermannTyton 4-way mounting base accommodates the T18 through T50 series cable ties. Insertion of the ties can be made from all four sides. Each mount may be secured with two screws, with adhesive backing, or both, for ease of application and stability.
Length (L)	1.12" / 28.5mm
Packaging Type	bag
Pkg. Qty.	100
Application	Mounting bases are used in conjunction with cable ties to stabilize and secure wiring bundles, both indoors and outdoors.
Application Method	Secured with two #8 screws.
Carton Qty.	5000
CSA Certified	No
Material Specification	RoHS
Operating Temperature	-40 Å°C to +85 Å°C, intermittent +105 Å°C (for 500 h)
ROHS Conformity	RoHS
Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes
UPC	089306023876
Width (W)	1.12" / 28.5mm
Max. Cable Tie Width	5.4mm
Height (H)	.19" / 4.8mm
Mounting Hole Å"	4.0mm
Mounting Hole Centers	20.0mm

- [Find a Distributor](#)
- [Get Product Samples](#)
- [Get Technical Drawings](#)