

118-00032



Article Number: 118-00032

Description: PEEK Cable Tie, 5.7" Long, 52lb Tensile Strength, PEEK, Beige, 100/pkg

Base Data	
Local Order Number	118-00032
Type	PT2A
Color	Beige (BGE)
Features and Benefits	<ul style="list-style-type: none"> <li>• PEEK cable ties provide excellent resistance to extreme temperature environments.</li> <li>• Contour style head design provides additional space in constrained areas and provides high tensile strength with very low insertion force.</li> </ul>
Quantity Per	bag
Product Description	HellermannTyton PEEK cable ties are made of a high performance material providing temperature resistance up to +464°F (+240°C). The contour style head design takes up less space making it ideal for space constrained areas and guarantees high tensile strength, as well as a low insertion force.
Short Description	PEEK Cable Tie, 5.7" Long, 52lb Tensile Strength, PEEK, Beige, 100/pkg
Product Dimensions	
Minimum Tensile Strength (Imperial)	52.0lbs
Minimum Tensile Strength (Metric)	230.0N
Length L (Imperial)	5.7"
Length L (Metric)	145.0mm
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.13"
Width W (Metric)	3.4mm
Bundle Diameter Min. (Imperial)	0.16"
Bundle Diameter Min. (Metric)	4.0mm
Bundle Diameter Max. (Imperial)	1.4"
Bundle Diameter Max. (Metric)	35.0mm

118-00032



Product Dimensions	Thickness T (Imperial)	0.05"
	Cable Tie Head Length (Imperial)	0.22"
	Cable Tie Head Width (Imperial)	0.24"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyetheretherketone (PEEK)
	Material Shortcut	PEEK
	Flammability	UL94 V0
	Operating Temperature	-67°F to +464°F (-55°C to +240°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Certification/Specification	DNV GL   EN 62275:2009	
Logistic and Packaging		
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	0.8kg