

161-64213



Article Number: 161-64213

Helawrap HWPP16 Sleeve, .63" Dia., Polypropylene, Black, 100.0ft/pkg



Base Data

Local Order Number 161-64213

Type HWPP16

Color Black (BK)

- Features and Benefits**
- Unique open design for easy branch-offs at any point along the harness.
 - Overwrap formation provides abrasion protection and accommodates multiple bundle configurations.
 - Flexible construction and design eliminates pinch points and minimizes bending fatigue, making it ideal for applications involving movement and vibration.
 - Split shape allows for future access without disassembly.

Product Description The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.

Variant Spiral Binding

Short Description Helawrap HWPP16 Sleeve, .63" Dia., Polypropylene, Black, 100.0ft/pkg

Product Dimensions

Bundle Diameter min (imperial) 0.55 "

Bundle Diameter min (metric) 13 mm

Bundle Diameter max (imperial) 0.63 "

Bundle Diameter max (metric) 16 mm

Diameter D (imperial) 0.5 "

Diameter D (metric) 14.0 mm

Nominal Diameter (imperial) 0.63 "

Nominal Diameter (metric) 16 mm

Wall Thickness WT (imperial) 0.031 "

Wall Thickness WT (metric) 0.80 mm

Pitch (imperial) 0.51 "

Pitch (metric) 13 mm

Logistics and Packaging

Quantity per carton

Package Quantity (imperial) 100.0 ft

Reel Length (metric) 30 m

Reel Length (imperial) 100.0 ft

Weight (imperial) 2.55 lbs

Weight (Metric) 1.16 kg

Material and Specifications

Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	UL94 HB
Halogenfree	Yes
Operating Temperature	-76 °F to +230 °F (-60 °C to +110 °C)
ROHS Conformity	Yes