

111-12211

Article Number: 111-12211

Description: Heavy-Duty Cable Tie, 11.8" Long, 120lb Tensile Strength, PA66, Natural, 50/pkg



Base Data	
Local Order Number	T120I9K2
Type	T120I
Color	Natural (NA)
Features and benefits	<ul style="list-style-type: none"> • Heavy duty design to offer higher tensile strength. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Quantity Per	bag
Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy-Duty Cable Tie, 11.8" Long, 120lb Tensile Strength, PA66, Natural, 50/pkg
Product Dimensions	
Minimum Tensile Strength (Imperial)	120.0lbs
Minimum Tensile Strength (Metric)	535.0N
Length L (Imperial)	11.8"
Length L (Metric)	300.0mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.3"
Width W (Metric)	7.6mm
Cable Tie Width Max. (Imperial)	0.3"
Cable Tie Width Max. (Metric)	7.61mm
Bundle Diameter Min. (Imperial)	0.2"

111-12211



Product Dimensions	Bundle Diameter Min. (Metric)	5.0mm
	Bundle Diameter Max. (Imperial)	3.2"
	Bundle Diameter Max. (Metric)	80.0mm
	Thickness T (Imperial)	0.06"
	Cable Tie Head Length (Imperial)	0.393"
	Cable Tie Head Width (Imperial)	0.502"
	Thickness T (Metric)	1.6mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 62275
	UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes	
Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50
	Customs Number(Schedule B)	3926909987