

Description: 18 AWG 2/C STR CM-CL2
Specifications: UL Standards 13 & 444; NEC Articles 725 & 800

Construction:

Conductor 18 19/.0092 Stranded Bare Copper
Insulation Polypropylene
Insulation Thickness 0.006" nom.
Insulation Colors Blk, Red
Insulation Diameter 0.058 nom.
Lay Length N/A

Jacket PVC
Jacket Thickness 0.015" nom.
Outside Diameter 0.148" nom.
Legend (Ink Print) **HONEYWELL P/N 1118 2C18 3038058 (ETL) CL2 OR CM C(ETL)US SUN RES (RoHS)**
W/O #XXXXXX-XXXXXX XXXX FT DEVICE/ZONE A B C D E F 1 2 3 4 5 6 7 8 9

Properties

Temperature Rating -20 to 60 °C
Operating Voltage 300 Volts max.
Capacitance 17 pf/ft nom.
Impedance 91 Ohms nom.
DC Resistance 6.5 Ohms/M' at 20°C
Flame Rating UL 1685 Vertical Tray