

Availability	Global
Operating Force (OF)	0,51 N m [4.5 in lb] max.
Full Overtravel Force	8,13 N m [6 in lb] max.
Release Force	0,08 N m [0.75 in lb] min.
Pretravel (PT)	20° max.
Overtravel (OT)	30° min.
Product Type	MICRO SWITCH™ Compact Limit Switches
Actuator	Side Rotary
Lever Type	1.5 in Fixed Length Lever with front mounted Steel Roller (.75 in dia. x .25 in wide)
Circuitry	1NC 1NO SPDT Snap Action, Double Break
Ampere Rating	10 A Ind./0.8 A Res./0.4 Res./0.1 A Res.
Supply Voltage	120 Vac, 240 Vac, 480 Vac/115 Vdc/230 Vdc/550 Vdc
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	Compact / Non Plug-In
Series Name	LS
Sealing	NEMA 1, 3, 4, 6, 13
Operating Temperature	-29 °C to 71 °C [-20 °F to 160 °F]
Comment	Switch is assembled for actuation in either direction. Operating head mounts in any of four positions.
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches
Sealed	Industrial