

Description: 16 AWG 2/C Home Theater Sound CM-CL2  
Specifications: UL Standards 13, & 444; NEC Article 725

**Construction:**

Conductor 16 AWG 26/30 Stranded Bare Copper  
Insulation Polypropylene  
Insulation Thickness 0.010" nom.  
Insulation Colors Blk,Red  
Insulation Diameter 0.078 nom.  
Lay Length N/A

Jacket PVC  
Jacket Thickness 0.017" nom.  
Outside Diameter 0.192" nom.  
Legend (Ink Print)

**HONEYWELL P/N 5250 2C16 3038058 (ETL) CL2 OR CM C(ETL)US SUN RES  
(RoHS) W/O# XXXXXX-XXXXXX XXXX FT RM# A B C D E F 1 2 3 4 5 6 7 8 9**

**Properties**

Temperature Rating -20 to 60 °C  
Operating Voltage 300 Volts max.  
Capacitance 22 pf/ft nom.  
Impedance 70 Ohms nom.  
DC Resistance 4.10 Ohms/M' at 20°C  
Flame Rating UL 1685 Vertical Tray