



## TH115 Series

This compact, stylish thermostat comes loaded with advanced programming features and a large backlit LCD



### MODELS & RATINGS

<b>TH115-A-120S</b>	2000 W @ 120 V	16.7 A resistive	60 Hz	4 wires / SPST
<b>TH115-A-240D</b>	3600 W @ 240 V	15 A resistive	60 Hz	4 wires / DPST
<b>TH115-A-240S</b>	4000 W @ 240 V	16.7 A resistive	60 Hz	4 wires / SPST

### SPECIFICATIONS

#### TEMPERATURE CONTROL

Microprocessor-optimized PIA  
 Heating cycles: 15 minutes  
 Accuracy: ± 0.5°C / 0.9°F

#### SWITCHING ACTION

Epoxy-soundproofed relay: Quiet operation

#### PROGRAMMING

7-day, 4 time periods/day, 2 temp. settings  
 Pre-programmed or personalized schedule  
 Early Start function  
 Selectable 12- or 24-hour clock / °C or °F

#### DIMENSIONS (H•W•D)

124 x 70 x 23 mm / 4.89 x 2.76 x 0.91 inches

### FEATURES

**Advanced temperature control** ensures total comfort by minimizing temperature swings

**ON/STANDBY** switch enables thermostat shutdown at end of heating season for added security

**Remote input** enables change of temperature modes from phone (Aube telephone controller required) or alarm/automation system with dry contact output

**On-screen heating power indicator** gives at-a-glance verification of power being used

**Temporary bypass** enables temperature override without changing programming

**Large, backlit LCD** features intuitive programming icons

**Attractive design** includes hidden programming buttons

**Battery-free backup** means no re-programming thermostat after power outage

### ACCESSORIES

Aube CT240 telephone controller  
 Aube CT241 telephone controller