

# TH135 Series

This easy-to-use electronic thermostat saves three temperature settings and is millivolt compatible



## MODEL & RATINGS

TH135-01

5 A (resistive) @ 24 V  
2 A (inductive) @ 24 V

R, W North America

Millivolt compatible

## SPECIFICATIONS

### TEMPERATURE CONTROL

PROPORTIONAL ADAPTIVE

Selectable cycles: 15 or 20 min.

CONVENTIONAL WITH ANTICIPATION

Accuracy:  $\pm 0.5^{\circ}\text{C} / 0.9^{\circ}\text{F}$

### TEMPERATURE SETTING

Manual

$^{\circ}\text{C}$  or  $^{\circ}\text{F}$  selectable

### POWER SUPPLY

2 AA batteries

### DIMENSIONS (H•W•D)

79 x 79 x 22 mm / 3.1 x 3.1 x 0.8 inches

## FEATURES

**Selectable temperature control** – gives thermostat flexibility to control a range of heating systems and applications

**Comfort, economy and vacation presets** – enable temperature changes at the touch of a button

**Pump protection** – for hot water heating activates pump for one minute every 24 hours to prevent seizure

**Compact design** – one of the smallest thermostats on the market

**Precise LCD** – shows room temperature in increments of  $0.1^{\circ}\text{C}$  or  $0.1^{\circ}\text{F}$

**Low battery indicator** – gives 60 days warning to replace batteries

**Remote input** enables change of temperature modes from phone (Aube telephone controller required) or alarm/automation system with dry contact output

## ACCESSORIES

Aube AC130-12 w all plate

Aube CT240 telephone controller

Aube RC840 electromechanical relay

Aube RC840T electromechanical relay