



TH141

This stylish thermostat features automatic changeover between heating and cooling



MODEL & RATINGS

TH141HC-28 1.5 A @ 24 V 2-, 3-, 4- or 5-wire installation (Rh, W, Rc, Y, G)

SPECIFICATIONS

TEMPERATURE CONTROL

PROPORTIONAL ADAPTIVE

Cycles: selectable 5, 10, 15 or 20 min.

CONVENTIONAL WITH ANTICIPATION

Programmable temp. span: $\pm 0.3^{\circ}\text{C}$ (0.5°F)
to $\pm 0.6^{\circ}\text{C}$ (1.1°F)

PROGRAMMING

7-day, up to 4 time periods, 2 temps. / day

Selectable 12- or 24-hour format, $^{\circ}\text{C}$ or $^{\circ}\text{F}$

POWER SUPPLY

2 AA batteries

DIMENSIONS (H•W•D)

126 x 97 x 26 mm / 4.9 x 3.8 x 1 in.

FEATURES

Selectable temperature control – gives thermostat flexibility to control a range of heating/cooling systems and applications

Automatic changeover between heating and cooling

Auto/manual fan control

Comfort, economy and vacation presets – enable temperature changes at the touch of a button

Armchair programming – convenient programming by removing faceplate from base

Precise LCD – shows room temperature in increments of 0.1°C or 0.1°F

Low battery indicator – gives 60 days warning to replace batteries

Remote input enables change of temperature modes from phone (Aube telephone controller required) or alarm/automation system (12 VDC transformer required)

ACCESSORIES

Aube CT240 telephone controller