

## Three-Phase—Type DT-3 60 Hz NEMA TP-1 Energy-Efficient Electrostatically Shielded—Aluminum Windings

2

## 480 Delta Volts to 240 Delta Volts with 120 Volt Lighting Tap on Phase B ①

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg) ②	Weathershield	Catalog Number
	FCAN	FCBN							
15	2 at +2.5%	4 at -2.5%	DT-3	150	912D	284B	220 (100)	WS38	V48M22E15EE
30	2 at +2.5%	4 at -2.5%	DT-3	150	912D	284B	293 (133)	WS38	V48M22E30EE
45	2 at +2.5%	4 at -2.5%	DT-3	150	912D	284B	348 (158)	WS38	V48M22E45EE
75	2 at +2.5%	4 at -2.5%	DT-3	150	914F	284B	554 (252)	WS39	V48M22E75EE
112.5	2 at +2.5%	4 at -2.5%	DT-3	150	916A	284B	820 (372)	WS19	V48M22E12EE
150	2 at +2.5%	4 at -2.5%	DT-3	150	916A	284B	940 (427)	WS19	V48M22E49EE
225	2 at +2.5%	4 at -2.5%	DT-3	150	917	284B	1421 (645)	WS34	V48M22E22EE
300	2 at +2.5%	4 at -2.5%	DT-3	150	923	284B	1787 (811)	WS37	V48M22E33EE
500	2 at +2.5%	4 at -2.5%	DT-3	150	919E	293A	2504 (1137)	WS35	V48M22E55EE
15	2 at +2.5%	4 at -2.5%	DT-3	115	912D	284B	231 (105)	WS38	V48M22F15EEES
30	2 at +2.5%	4 at -2.5%	DT-3	115	912D	284B	326 (148)	WS38	V48M22F30EEES
45	2 at +2.5%	4 at -2.5%	DT-3	115	912D	284B	397 (180)	WS38	V48M22F45EEES
75	2 at +2.5%	4 at -2.5%	DT-3	115	914F	284B	615 (279)	WS39	V48M22F75EEES
112.5	2 at +2.5%	4 at -2.5%	DT-3	115	916A	284B	805 (365)	WS19	V48M22F12EEES
150	2 at +2.5%	4 at -2.5%	DT-3	115	916A	284B	1012 (459)	WS19	V48M22F49EEES
225	2 at +2.5%	4 at -2.5%	DT-3	115	918A	284B	1589 (721)	WS34	V48M22F22EEES
300	2 at +2.5%	4 at -2.5%	DT-3	115	923	284B	1782 (809)	WS37	V48M22F33EEES
500	2 at +2.5%	4 at -2.5%	DT-3	115	920E	293A	3117 (1415)	WS35	V48M22F55EEES
15	2 at +2.5%	4 at -2.5%	DT-3	80	912D	284B	294 (133)	WS38	V48M22B15EEES
30	2 at +2.5%	4 at -2.5%	DT-3	80	912D	284B	374 (170)	WS38	V48M22B30EEES
45	2 at +2.5%	4 at -2.5%	DT-3	80	914F	284B	586 (266)	WS39	V48M22B45EEES
75	2 at +2.5%	4 at -2.5%	DT-3	80	916A	284B	807 (366)	WS19	V48M22B75EEES
112.5	2 at +2.5%	4 at -2.5%	DT-3	80	916A	284B	1005 (456)	WS19	V48M22B12EEES
150	2 at +2.5%	4 at -2.5%	DT-3	80	917	284B	1170 (531)	WS34	V48M22B49EEES
225	2 at +2.5%	4 at -2.5%	DT-3	80	923	284B	1764 (801)	WS37	V48M22B22EEES
300	2 at +2.5%	4 at -2.5%	DT-3	80	919E	293A	2317 (1052)	WS35	V48M22B33EEES

**Notes**

① Lighting tap limited to 5% of nameplate full load capacity.

② Weights subject to change.

For other ratings or catalog numbers not shown, or for special enclosure types (including stainless steel), refer to Eaton. Frame drawings/dimensions information begins on **Page V2-T2-216**.