



Dependable Power for Any Application

Product Datasheet

220 X 440 Primary Volts - 110/115/120 Secondary Volts - 1Ø Industrial Control Transformer - Open Core & Coil

Catalog #: TB81211



PRODUCT FEATURES

- Meets or exceeds UL, CSA, NEMA, and ANSI standards
- UL Listed and CSA Certified
- Meets NEC Article 450
- Constructed out of electrical lamination with precision wound coils
- Primary and secondary fuse kits easily adaptable
- Add suffix "F2" to catalog for factory installed 2 pole primary block
- Add suffix "F3" to catalog for factory installed 3 pole primary and secondary block
- Covered under Acme's 10 year limited warranty

BENEFITS

- Series parallel connecting links save time and costs
- Mounting plate adapts to various mounting dimensions
- Molded terminal blocks allow easy ring terminal installation
- Optional Secondary Fuse Kits available

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	100
Primary Voltage:	220 X 440
Secondary Voltage:	110/115/120
Frequency:	50/60 Hz
Max Temperature Rise:	80°C
UL Insulation Class:	130°C

PRODUCT MEASUREMENTS

Height (In./cm):	2.70 (6.8)
Width (In./cm):	3.00 (7.6)
Depth (In./cm):	4.90 (12.4)

CONFIGURATION

Mounting Type:	Floor
Primary Fuse Block:	PL112700
Wiring Diagram:	B

PACKAGING

Ship Weight (Lbs/Kg):	4 (1.8)
-----------------------	---------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 66
CSA Listed:	LR7357-16
Warranty:	Acme Electric Warranty Card www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf