



Drip Shields



Hole Seals

FEATURES-SPECIFICATIONS

DRIP SHIELDS

- Designed to protect door hardware from dripping water and settling dust
- Drip shields attach easily to the enclosure with stainless steel screws, gasket and sealing washers (hardware is furnished)
- Drip shields fit all single door NEMA 12 and NEMA 4 wall mounted enclosures
- Stainless steel door clamps are furnished to replace the standard door clamps
- Steel drip shields have a ANSI 61 gray polyester powder finish over phosphatized surfaces
- Stainless steel drip shields have a grained finish
- 42", 48", 60" and 72" drip shields fit floor mounted double door enclosures. Specify when ordering for double door wall mounted enclosures

HOLE SEALS

Designed to seal extra push-button holes, conduit openings, and knockout openings from dirt, dust, oil and water

Steel:

- Quick wing nut
- Oil resistant gasket
- ANSI 61 gray polyester powder

Stainless Steel:

- Quick wing nut
- Oil resistant gasket
- Grained finish

DRIP SHIELDS			
CATALOG NUMBER		GAUGE	FITS ENCLOSURE WIDTH
STEEL	STAINLESS STEEL		
DK12	SSDK12	14	12.00 (305)
DK16	SSDK16	14	16.00 (406)
DK20	SSDK20	14	20.00 (508)
DK24	SSDK24	14	24.00 (610)
DK30	SSDK30	14	30.00 (762)
DK36	SSDK36	14	36.00 (914)
DK42	—	14	42.00 (1067)
DK48	—	14	48.00 (1219)
DK60	—	14	60.00 (1524)
DK72	—	14	72.00 (1829)

HOLE SEALS			
CATALOG NUMBER		DESCRIPTION	HOLE DIAMETER
STEEL	STAINLESS STEEL		
WASPBG	WASPBGSS	Miniature oil tight pushbutton holes	0.88 (22)
WAS050	WAS050SS	1/2-inch conduit holes	0.88 (22)
WAS075	WAS075SS	3/4-inch conduit holes	1.13 (29)
WASPB	WASPBSS	Standard oil-tight pushbutton holes	1.20 (30)
WAS100	WAS100SS	1-inch conduit holes	1.38 (35)
WAS125	WAS125SS	1 1/4-inch conduit holes	1.63 (41)
WAS150	WAS150SS	1 1/2-inch conduit holes	2.00 (51)
WAS200	WAS200SS	2-inch conduit holes	2.50 (64)
WAS250	—	2 1/2-inch conduit holes	3.00 (76)
WAS300	—	3-inch conduit holes	3.63 (92)
WAS350	—	3 1/2-inch conduit holes	4.00 (102)
WAS400	—	4-inch conduit holes	4.63 (118)

PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE
WA90SMP20G	C31	WAL12AR	J2-J19	WAPWK1711SS	J5	WBP2020	B10-B13
WA90SP36F3	I8-I12	WAL12B	J2-J19	WAPWK2315NF	J5	WBP2418	B10-B13
WA90SP36F3G	C31	WAL12KEY	J2-23	WAPWK2315SS	J5	WBP2420	B10-B13
WA90SP36F4	I8-I12	WAL1A	J2-J19	WAPWK2919NF	J5	WBP2424	B10-B13
WA90SP36F4G	C31	WAL1B	J2-J19	WAPWK3523NF	J5	WBP3024	B10-B13
WA90XM3918SSN4	F49	WAL1C	J2-J19	WARAK24	I13, J12	WBP3030DD	B10-B13
WA90XM3920SSN4	F49	WAL1D	J2-J19	WARAK30	I13, J12	WBP3044DD	B10-B13
WA90XM3920U	F34	WAL23	J2-J19	WARAK36	I13, J12	WBP3236DD	B10-B13
WA90XM3924SSN4	F49	WAL23SS	J2-J19	WAS050	J4	WBP3624	B10-B13
WA90XM3924U	F34	WAL23SSA	J2-23	WAS050SS	J4	WBP3630	B10-B13
WA90XM3924U	F34	WAL2A	J2-J19	WAS075	J4	WBP3636DD	B10-B13
WA90XM7718SSN4	F49	WAL2B	J2-J19	WAS075SS	J4	WBP4242DD	B10-B13
WA90XM7720SSN4	F49	WAL2C	J2-23	WAS100	J4	WBP4848DD	B10-B13
WA90XM7720U	F34	WAL2D	J2-J19	WAS100SS	J4	WC08C08	H12
WA90XM7724SSN4	F49	WAL3A	J2-23	WAS125	J4	WC08C08SS	E14
WA90XM7724U	F34	WAL3ASS	J15	WAS125SS	J4	WC08C12	H12
WABN4JIC	J2-23	WAL3B	J2-23	WAS150	J4	WC08C12SS	E14
WACLJIC	J2-23	WAL3BSS	J15	WAS150SS	J4	WC08C16	H12
WACLKEY	J2-23	WAL3C	J2-23	WAS200	J4	WC08C16SS	E14
WACLSN12	J2-J19	WAL3CSS	J15	WAS200SS	J4	WC08C20	H12
WACSHELF12	J2-J19	WAL3D	J2-23	WAS250	J4	WC08C20SS	E14
WACSHELF18	J2-J19	WAL3DSS	J15	WAS300	J4	WC10B	H2-H10
WADSTOPK	J3	WAL4A	J2-23	WAS350	J4	WC10C	J2-23
WAEK115	J7	WAL4B	J2-23	WAS400	J4	WC10T	H2-H10
WAEK115NDH	J7	WAL4C	J2-23	WASPB	J4	WC10W	H2-H10
WAEKDF	J7	WAL4D	J2-23	WASPBG	J4	WC1224B	H2-H10
WAEMKA4	J2-23	WAL8	J2-J19	WASPBGSS	J4	WC1224T	H2-H10
WAENST	J2-23	WAMFK3RL014	B9	WASPSS	J4	WC1224W	H2-H10
WAEXG275	K24-K42	WAMFK3RL016	B9	WAVK0203	J2-J19	WC1248BD	H2-H10
WAFLT33	J2-J19	WAN12RA	J2-23	WAVK0203SSA	K27	WC1248T	H2-H10
WAFLT34	J2-J19	WAN4XRA	J2-23	WAVK0303	J2-J19	WC1248W	H2-H10
WAFLT44	J2-J19	WANADFK	J2-23	WAVK0303SSA	K27	WC12B	H2-H10
WAFLT64	J2-J19	WAPLKJIC	J2-23	WAVK0304	J2-J19	WC12C	J2-23
WAFLT66	J2-J19	WAPMK3RL014	B9	WAVK0304SSA	K27	WC12C12	H12
WAFLT812	J2-J19	WAPMK3RL016	B9	WAVK0404	J2-J19	WC12C12SS	E14
WAFLT86	J2-J19	WAPPL0606	J2-J19	WAVK0404SSA	K27	WC12C16	H12
WAFLT88	J2-J19	WAPPL0810	J2-J19	WAVK0604	J2-J19	WC12C16SS	E14
WAFMP10	J2-J19	WAPS03	J2-J19	WAVK0604SSA	K27	WC12C20	H12
WAFMP4	J2-J19	WAPS09	J2-J19	WAVK0606	J2-J19	WC12C20SS	E14
WAFMP6	J2-J19	WAPS1420CN	J2-23	WAVK0606SSA	K27	WC12C24	H12
WAFT44XSS	J2-J19	WAPS3816CN	J2-23	WAVK0806	J2-J19	WC12C24SS	E14
WAFT44XSSA	J2-J19	WAPWK0503NF	J5	WAVK0806SSA	K27	WC12T	H2-H10
WAGARD10	K24-K42	WAPWK0503SS	J5	WAVK0808	J2-J19	WC12W	H2-H10
WAGARD4	K24-K42	WAPWK0905NF	J5	WAVK0808SSA	K27	WC1436B	H2-H10
WAGARD6	K24-K42	WAPWK0905SS	J5	WAVK0812	J2-J19	WC1436P1	H2-H10
WAGSE	J2-J19	WAPWK1308NF	J5	WAVK0812SSA	K27	WC1436P2	H2-H10
WAJCDFK	J2-J19	WAPWK1308SS	J5	WAVE	J2-J19	WC1436P3	H2-H10
WAJICRA	J2-J19	WAPWK1705NF	J5	WAX10	J2-J19	WC1436T	H2-H10
WAKP529A	K24-K42	WAPWK1711NF	J5	WBP1812	B10-B13	WC1436W	H2-H10