



**Drip Shields**



**Hole Seals**

**FEATURES-SPECIFICATIONS**

**DRIP SHIELDS**

- Designed to protect door hardware from dripping water and settling dust
- Drip shields attach easily to the enclosure with stainless steel screws, gasket and sealing washers (hardware is furnished)
- Drip shields fit all single door NEMA 12 and NEMA 4 wall mounted enclosures
- Stainless steel door clamps are furnished to replace the standard door clamps
- Steel drip shields have a ANSI 61 gray polyester powder finish over phosphatized surfaces
- Stainless steel drip shields have a grained finish
- 42", 48", 60" and 72" drip shields fit floor mounted double door enclosures. Specify when ordering for double door wall mounted enclosures

**HOLE SEALS**

Designed to seal extra push-button holes, conduit openings, and knockout openings from dirt, dust, oil and water

**Steel:**

- Quick wing nut
- Oil resistant gasket
- ANSI 61 gray polyester powder

**Stainless Steel:**

- Quick wing nut
- Oil resistant gasket
- Grained finish

<b>DRIP SHIELDS</b>			
<b>CATALOG NUMBER</b>		<b>GAUGE</b>	<b>FITS ENCLOSURE WIDTH</b>
<b>STEEL</b>	<b>STAINLESS STEEL</b>		
<b>DK12</b>	<b>SSDK12</b>	14	12.00 (305)
<b>DK16</b>	<b>SSDK16</b>	14	16.00 (406)
<b>DK20</b>	<b>SSDK20</b>	14	20.00 (508)
<b>DK24</b>	<b>SSDK24</b>	14	24.00 (610)
<b>DK30</b>	<b>SSDK30</b>	14	30.00 (762)
<b>DK36</b>	<b>SSDK36</b>	14	36.00 (914)
<b>DK42</b>	—	14	42.00 (1067)
<b>DK48</b>	—	14	48.00 (1219)
<b>DK60</b>	—	14	60.00 (1524)
<b>DK72</b>	—	14	72.00 (1829)

<b>HOLE SEALS</b>			
<b>CATALOG NUMBER</b>		<b>DESCRIPTION</b>	<b>HOLE DIAMETER</b>
<b>STEEL</b>	<b>STAINLESS STEEL</b>		
<b>WASPBG</b>	<b>WASPBGSS</b>	Miniature oil tight pushbutton holes	0.88 (22)
<b>WAS050</b>	<b>WAS050SS</b>	1/2-inch conduit holes	0.88 (22)
<b>WAS075</b>	<b>WAS075SS</b>	3/4-inch conduit holes	1.13 (29)
<b>WASPB</b>	<b>WASPBSS</b>	Standard oil-tight pushbutton holes	1.20 (30)
<b>WAS100</b>	<b>WAS100SS</b>	1-inch conduit holes	1.38 (35)
<b>WAS125</b>	<b>WAS125SS</b>	1 1/4-inch conduit holes	1.63 (41)
<b>WAS150</b>	<b>WAS150SS</b>	1 1/2-inch conduit holes	2.00 (51)
<b>WAS200</b>	<b>WAS200SS</b>	2-inch conduit holes	2.50 (64)
<b>WAS250</b>	—	2 1/2-inch conduit holes	3.00 (76)
<b>WAS300</b>	—	3-inch conduit holes	3.63 (92)
<b>WAS350</b>	—	3 1/2-inch conduit holes	4.00 (102)
<b>WAS400</b>	—	4-inch conduit holes	4.63 (118)

PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE
WA90SMP20G	C31	WAL12AR	J2-J19	WAPWK1711SS	J5	WBP2020	B10-B13
WA90SP36F3	I8-I12	WAL12B	J2-J19	WAPWK2315NF	J5	WBP2418	B10-B13
WA90SP36F3G	C31	WAL12KEY	J2-23	WAPWK2315SS	J5	WBP2420	B10-B13
WA90SP36F4	I8-I12	WAL1A	J2-J19	WAPWK2919NF	J5	WBP2424	B10-B13
WA90SP36F4G	C31	WAL1B	J2-J19	WAPWK3523NF	J5	WBP3024	B10-B13
WA90XM3918SSN4	F49	WAL1C	J2-J19	WARAK24	I13, J12	WBP3030DD	B10-B13
WA90XM3920SSN4	F49	WAL1D	J2-J19	WARAK30	I13, J12	WBP3044DD	B10-B13
WA90XM3920U	F34	WAL23	J2-J19	WARAK36	I13, J12	WBP3236DD	B10-B13
WA90XM3924SSN4	F49	WAL23SS	J2-J19	WAS050	J4	WBP3624	B10-B13
WA90XM3924U	F34	WAL23SSA	J2-23	WAS050SS	J4	WBP3630	B10-B13
WA90XM3924U	F34	WAL2A	J2-J19	WAS075	J4	WBP3636DD	B10-B13
WA90XM3924U	F34	WAL2B	J2-J19	WAS075SS	J4	WBP4242DD	B10-B13
WA90XM7718SSN4	F49	WAL2C	J2-23	WAS100	J4	WBP4848DD	B10-B13
WA90XM7720SSN4	F49	WAL2D	J2-J19	WAS100SS	J4	WC08C08	H12
WA90XM7720U	F34	WAL2D	J2-J19	WAS125	J4	WC08C08SS	E14
WA90XM7724SSN4	F49	WAL3A	J2-23	WAS125SS	J4	WC08C12	H12
WA90XM7724U	F34	WAL3ASS	J15	WAS150	J4	WC08C12SS	E14
WABN4JIC	J2-23	WAL3B	J2-23	WAS150SS	J4	WC08C16	H12
WACLJIC	J2-23	WAL3BSS	J15	WAS200	J4	WC08C16SS	E14
WACLKEY	J2-23	WAL3C	J2-23	WAS200SS	J4	WC08C20	H12
WACLSN12	J2-J19	WAL3CSS	J15	WAS250	J4	WC08C20SS	E14
WACSHELF12	J2-J19	WAL3D	J2-23	WAS300	J4	WC10B	H2-H10
WACSHELF18	J2-J19	WAL3DSS	J15	WAS350	J4	WC10C	J2-23
WADSTOPK	J3	WAL4A	J2-23	WAS400	J4	WC10T	H2-H10
WAEK115	J7	WAL4B	J2-23	WASPB	J4	WC10W	H2-H10
WAEK115NDH	J7	WAL4C	J2-23	WASPBG	J4	WC1224B	H2-H10
WAEKDF	J7	WAL4D	J2-23	WASPBGSS	J4	WC1224T	H2-H10
WAEMKA4	J2-23	WAL8	J2-J19	WASPSS	J4	WC1224W	H2-H10
WAENST	J2-23	WAMFK3RL014	B9	WAVK0203	J2-J19	WC1248BD	H2-H10
WAEXG275	K24-K42	WAMFK3RL016	B9	WAVK0203SSA	K27	WC1248T	H2-H10
WAFLT33	J2-J19	WAN12RA	J2-23	WAVK0303	J2-J19	WC1248W	H2-H10
WAFLT34	J2-J19	WAN4XRA	J2-23	WAVK0303SSA	K27	WC12B	H2-H10
WAFLT44	J2-J19	WANADFK	J2-23	WAVK0304	J2-J19	WC12C	J2-23
WAFLT64	J2-J19	WAPLKJIC	J2-23	WAVK0304SSA	K27	WC12C12	H12
WAFLT66	J2-J19	WAPMK3RL014	B9	WAVK0404	J2-J19	WC12C12SS	E14
WAFLT812	J2-J19	WAPMK3RL016	B9	WAVK0404SSA	K27	WC12C16	H12
WAFLT86	J2-J19	WAPPL0606	J2-J19	WAVK0604	J2-J19	WC12C16SS	E14
WAFLT88	J2-J19	WAPPL0810	J2-J19	WAVK0604SSA	K27	WC12C20	H12
WAFMP10	J2-J19	WAPS03	J2-J19	WAVK0606	J2-J19	WC12C20SS	E14
WAFMP4	J2-J19	WAPS09	J2-J19	WAVK0606SSA	K27	WC12C24	H12
WAFMP6	J2-J19	WAPS1420CN	J2-23	WAVK0806	J2-J19	WC12C24SS	E14
WAFT44XSS	J2-J19	WAPS3816CN	J2-23	WAVK0806SSA	K27	WC12T	H2-H10
WAFT44XSSA	J2-J19	WAPWK0503NF	J5	WAVK0808	J2-J19	WC12W	H2-H10
WAGARD10	K24-K42	WAPWK0503SS	J5	WAVK0808SSA	K27	WC1436B	H2-H10
WAGARD4	K24-K42	WAPWK0905NF	J5	WAVK0812	J2-J19	WC1436P1	H2-H10
WAGARD6	K24-K42	WAPWK0905SS	J5	WAVK0812SSA	K27	WC1436P2	H2-H10
WAGSE	J2-J19	WAPWK1308NF	J5	WAVE	J2-J19	WC1436P3	H2-H10
WAJCDFK	J2-J19	WAPWK1308SS	J5	WAX10	J2-J19	WC1436T	H2-H10
WAJICRA	J2-J19	WAPWK1705NF	J5	WBP1812	B10-B13	WC1436W	H2-H10
WAKP529A	K24-K42	WAPWK1711NF	J5				