

<b>JW SERIES FEED THROUGH WIREWAY (FITTINGS)</b>				
CATALOG NUMBER				DESCRIPTION
2.50 x 2.50 (64 x 64)	4.00 x 4.00 (102 x 102)	6.00 x 6.00 (152 x 152)	8.00 x 8.00 (203 x 203)	
JWS2	JWS4	JWS6	JWS8	Telescope*
JWF2	JWF4	JWF6	JWF8	Cut-off (1 set of gaskets and screws included)
JWL902	JWL904	JWL906	JWL908	90 Degree elbow (1 set of gaskets and screws included)
JWL452	JWL454	JWL456	JWL458	45 Degree elbow (1 set of gaskets and screws included)
JWT2	JWT4	JWT6	JWT8	Tee-top (2 sets of gaskets and screws included)
JWX2	JWX4	JWX6	JWX8	Cross (3 sets of gaskets and screws included)
JWE2	JWE4	JWE6	JWE8	End plate (1 set of gaskets and screws included)
JWA2	JWA4	JWA6	JWA8	Box adaptor (1 set of gaskets and screws included)
—	JWRB42C	—	—	Reducer 4.00" (102) to 2.50" (54) center hole**
—	—	JWRB64C	—	Reducer 6.00" (152) to 4.00" (102) center hole**
—	—	—	JWRB84C	Reducer 8.00" (203) to 4.00" (102) center hole**
—	—	—	JWRB86C	Reducer 8.00"(203) to 6.00" (152) center hole**
JWD2	JWD4	JWD6	JWD8	Drop-hanger
JWBH2	JWBH4	JWBH6	JWBH8	Bracket-hanger
JWN221	JWN441	JWN661	JWN881	1.00" Nipple
JWN222	JWN442	JWN662	JWN882	2.00" Nipple
JWN223	JWN443	JWN663	JWN883	3.00" Nipple
JWN226	JWN446	JWN666	JWN886	6.00" Nipple
JWSC22	JWSC44	JWSC66	—	Swivel nipple-regular
JWFF2	JWFF4	JWFF6	JWFF8	Flexible fitting***
—	JW4BK60	JW6BK60	JW8BK60	60.00" Barrier kit
JWG22	JWG44	JWG66	JWG88	Extra gasket and screws

\*Not UL listed.

\*\*One set of gaskets and screws included with all reducers.

\*\*\*Minimum length 3", maximum length 8".

<b>JW SERIES WIREWAY &amp; FITTINGS DIMENSIONS</b>																		
A X B	C - LENGTH						D	E	F	G	H	J	K	P	R	S	T	U
2.50x2.50 (64x64)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	3.88 (99)	3.88 (99)	5.50 (140)	8.50 (216)	2.50 (64)	2.00 (51)	4.25 (108)	4.63 (118)	3.75 (95)	9.31 (236)	4.50 (114)	4.38 (111)
4.00x4.00 (102x102)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	5.38 (137)	5.38 (137)	7.00 (178)	10.00 (254)	3.25 (83)	2.44 (62)	5.00 (127)	6.13 (156)	3.75 (95)	11.75 (298)	6.00 (152)	5.88 (149)
6.00x6.00 (152x152)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	7.63 (194)	7.63 (194)	9.00 (229)	12.00 (305)	4.25 (108)	3.00 (76)	6.00 (152)	8.25 (210)	3.75 (95)	15.25 (387)	8.13 (207)	7.88 (200)
8.00x8.00 (203x203)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	9.63 (245)	9.63 (245)	11.00 (279)	14.00 (356)	5.25 (133)	3.75 (95)	7.00 (178)	10.25 (260)	3.75 (95)	20.56 (522)	12.13 (308)	9.88 (251)

PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE
HW-MP2016CS	E50-E79	HW-N4X302006CH	E50-E79	HW-WM1610CS	E50-E79	JW83	G12
HW-MP2016FG	E50-E79	HW-N4X302008CH	E50-E79	HW-WM2016A	E50-E79	JW84	G12
HW-MP2016SS	E50-E79	HW-N4X302010CH	E50-E79	HW-WM2016CS	E50-E79	JW85	G12
HW-MP604A	E50-E79	HW-N4X302012CH	E50-E79	HW-WM2412A	E50-E79	JW8BK60	G12
HW-MP604CS	E50-E79	HW-N4X302408CH	E50-E79	HW-WM2412CS	E50-E79	JWA2	G12
HW-MP604FG	E50-E79	HW-N4X302410CH	E50-E79	HW-WM2420A	E50-E79	JWA4	G12
HW-MP604SS	E50-E79	HW-N4X302412CH	E50-E79	HW-WM2420CS	E50-E79	JWA6	G12
HW-MP606A	E50-E79	HW-N4X332	E50-E79	HW-WM2424A	E50-E79	JWA8	G12
HW-MP606CS	E50-E79	HW-N4X363008CH	E50-E79	HW-WM2424CS	E50-E79	JWBH2	G12
HW-MP606FG	E50-E79	HW-N4X363010CH	E50-E79	HW-WM3020A	E50-E79	JWBH4	G12
HW-MP606SS	E50-E79	HW-N4X363012CH	E50-E79	HW-WM3020CS	E50-E79	JWBH6	G12
HW-MP706A	E50-E79	HW-N4X3PB	E50-E79	HW-WM3024A	E50-E79	JWBH8	G12
HW-MP706CS	E50-E79	HW-N4X3PB-22	E50-E79	HW-WM3024CS	E50-E79	JWD2	G12
HW-MP806A	E50-E79	HW-N4X483612CH	E50-E79	HW-WM3630A	E50-E79	JWD4	G12
HW-MP806CS	E50-E79	HW-N4X483616CH	E50-E79	HW-WM3630CS	E50-E79	JWD6	G12
HW-MP806FG	E50-E79	HW-N4X4PB	E50-E79	HW-WM3636A	E50-E79	JWD8	G12
HW-MP806SS	E50-E79	HW-N4X4PB-22	E50-E79	HW-WM3636CS	E50-E79	JWE2	G12
HW-MP808CS	E50-E79	HW-N4X4PBW	E50-E79	HW-WM3648A	E50-E79	JWE4	G12
HW-MP808FG	E50-E79	HW-N4X532	E50-E79	HW-WM3648CS	E50-E79	JWE6	G12
HW-MP808SS	E50-E79	HW-N4X5PB	E50-E79	HW-WM4836A	E50-E79	JWE8	G12
HW-MP906CS	E50-E79	HW-N4X5PB-22	E50-E79	HW-WM4836CS	E50-E79	JWF2	G12
HW-N3R242410CH	E50-E79	HW-N4X603612CH	E50-E79	HW-WM6036A	E50-E79	JWF4	G12
HW-N3R302008CH	E50-E79	HW-N4X603616CH	E50-E79	HW-WM6036CS	E50-E79	JWF6	G12
HW-N3R302010CH	E50-E79	HW-N4X644	E50-E79	JIC040202	C14	JWF8	G12
HW-N3R302410CH	E50-E79	HW-N4X6PB	E50-E79	JIC0403025	C14	JWFF2	G12
HW-N3R302412CH	E50-E79	HW-N4X6PB-22	E50-E79	JIC040403	C14	JWFF4	G12
HW-N3R363008CH	E50-E79	HW-N4X6PBW	E50-E79	JW21	G12	JWFF6	G12
HW-N3R363010CH	E50-E79	HW-N4X763SC	E50-E79	JW210	G12	JWFF8	G12
HW-N3R363012CH	E50-E79	HW-N4X7PB	E50-E79	JW22	G12	JWG22	G12
HW-N3R483612CH	E50-E79	HW-N4X7PB-22	E50-E79	JW23	G12	JWG44	G12
HW-N3R483616CH	E50-E79	HW-N4X832	E50-E79	JW24	G12	JWG66	G12
HW-N4X1144	E50-E79	HW-N4X844	E50-E79	JW25	G12	JWG88	G12
HW-N4X12PBW	E50-E79	HW-N4X932	E50-E79	JW41	G12	JWL452	G12
HW-N4X1432	E50-E79	HW-N4X963SC	E50-E79	JW410	G12	JWL454	G12
HW-N4X161007CH	E50-E79	HW-N4X9PBW	E50-E79	JW42	G12	JWL456	G12
HW-N4X16PBW	E50-E79	HW-N4XMTGFTKIT	E50-E79	JW43	G12	JWL458	G12
HW-N4X1732	E50-E79	HW-SN1610FG	E50-E79	JW44	G12	JWL902	G12
HW-N4X1PB	E50-E79	HW-SN2016FG	E50-E79	JW45	G12	JWL904	G12
HW-N4X1PB-22	E50-E79	HW-SN2412FG	E50-E79	JW4BK60	G12	JWL906	G12
HW-N4X201612CH	E50-E79	HW-SN2424FG	E50-E79	JW61	G12	JWL908	G12
HW-N4X20PBW	E50-E79	HW-SN3024FG	E50-E79	JW610	G12	JWN221	G12
HW-N4X241206CH	E50-E79	HW-SN3630FG	E50-E79	JW62	G12	JWN222	G12
HW-N4X241210CH	E50-E79	HW-SNBP1610S	E50-E79	JW63	G12	JWN223	G12
HW-N4X242008CH	E50-E79	HW-SNBP2016S	E50-E79	JW64	G12	JWN226	G12
HW-N4X242410CH	E50-E79	HW-SNBP2412S	E50-E79	JW65	G12	JWN441	G12
HW-N4X242412CH	E50-E79	HW-SNBP2424S	E50-E79	JW6BK60	G12	JWN442	G12
HW-N4X25PBW	E50-E79	HW-SNBP3024S	E50-E79	JW81	G12	JWN443	G12
HW-N4X2PB	E50-E79	HW-SNBP3630S	E50-E79	JW810	G12	JWN446	G12
HW-N4X2PB-22	E50-E79	HW-WM1610A	E50-E79	JW82	G12	JWN661	G12