

GROUP M



600 DELTA PRIMARY VOLTS — 480Y/277 SECONDARY VOLTS — 3Ø, 60 Hz

| kVA | CATALOG NO. | APPROX. DIMENSIONS Inches (Cm.) | | | APPROX. SHIP WEIGHT Lbs. (Kg.) | TYPE MTG. W – Wall F – Floor | KNOCKOUTS Inches (Cm.) | WEATHER SHIELD P/N | Wiring Diagrams & Design Figures Begin on Page 154 |
|-------|-------------|------------------------------------|--------------|--------------|--------------------------------------|------------------------------------|---------------------------|--------------------------|--|
| | | HEIGHT | WIDTH | DEPTH | | | | | |
| 3.0 | T2A795161S | 10.38 (26.4) | 12.37 (31.4) | 7.47 (19.0) | 75 (34.0) | W | 0.75-1.25 (1.9-3.2) | NA | 55-F |
| 6.0 | T2A795171S | 11.83 (30.0) | 14.17 (36.0) | 8.82 (22.4) | 140 (63.5) | W | 0.75-1.25 (1.9-3.2) | NA | 55-F |
| 9.0 | T2A795181S | 14.03 (38.8) | 17.77 (45.1) | 11.52 (29.3) | 180 (81.6) | W | 0.75-1.25 (1.9-3.2) | NA | 55-F |
| 15.0 | T3795191S | 18.86 (47.9) | 20.30 (51.6) | 9.03 (22.9) | 250 (113.0) | F ① | NA | NA | 55-I |
| 30.0 | TP795203S | 29.41 (74.7) | 28.15 (71.5) | 22.37 (56.8) | 400 (181.0) | F ① | NA | WSA2 | 51-E |
| 45.0 | TP795213S | 29.41 (74.7) | 28.15 (71.5) | 22.37 (56.8) | 425 (193.0) | F ① | NA | WSA2 | 51-E |
| 75.0 | TP795223S | 29.41 (74.7) | 28.15 (71.5) | 22.37 (56.8) | 700 (318.0) | F ① | NA | WSA2 | 51-E |
| 112.5 | TP795233S | 35.47 (90.1) | 31.90 (81.0) | 26.88 (68.3) | 750 (340.0) | F | NA | WSA3 | 51-E |
| 150.0 | TP795243S | 41.52 (105.5) | 32.90 (83.6) | 29.87 (75.9) | 1125 (510.0) | F | NA | WSA4 | 51-E |

Notes: 3.0 through 15.0 kVA units are encapsulated (TP1 exempt), 30.0 through 150.0 kVA are TP1 compliant

GROUP O

208 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz

| kVA | CATALOG NO. | APPROX. DIMENSIONS Inches (Cm.) | | | APPROX. SHIP WEIGHT Lbs. (Kg.) | TYPE MTG. W – Wall F – Floor | KNOCKOUTS Inches (Cm.) | WEATHER SHIELD P/N | Wiring Diagrams & Design Figures Begin on Page 154 |
|------|-------------|------------------------------------|--------------|--------------|--------------------------------------|------------------------------------|---------------------------|--------------------------|--|
| | | HEIGHT | WIDTH | DEPTH | | | | | |
| 3.0 | T2A792681S | 10.38 (26.4) | 12.37 (31.4) | 7.47 (19.0) | 75 (34.0) | W | 0.75-1.25 (1.9-3.2) | NA | 60-F |
| 6.0 | T2A792691S | 11.83 (30.0) | 14.17 (36.0) | 8.82 (22.4) | 140 (63.5) | W | 0.75-1.25 (1.9-3.2) | NA | 60-F |
| 9.0 | T2A792701S | 14.03 (36.0) | 17.77 (45.1) | 11.52 (29.3) | 180 (81.6) | W | 0.75-1.25 (1.9-3.2) | NA | 60-F |
| 15.0 | T3-792711S | 18.86 (48.0) | 20.30 (51.6) | 9.03 (22.9) | 245 (111.0) | F ① | NA | NA | 60-I |
| 30.0 | TP792724S | 25.50 (64.8) | 24.39 (61.9) | 19.37 (49.2) | 300 (136.0) | F ① | NA | WSA1 | 61-E |
| 45.0 | TP792734S | 25.48 (64.7) | 24.39 (61.9) | 19.37 (49.2) | 365 (166.0) | F ① | NA | WSA1 | 61-E |
| 75.0 | TP792744S | 29.41 (74.7) | 28.15 (71.5) | 22.37 (56.8) | 500 (227.0) | F ① | NA | WSA2 | 61-E |

Notes: 3.0 through 15.0 kVA units are encapsulated (TP1 exempt), 30.0 through 75.0 kVA units are TP1 compliant

GROUP P

600 DELTA PRIMARY VOLTS — 240 DELTA/120 TAP SECONDARY VOLTS — 3Ø, 60 Hz

| kVA | CATALOG NO. | APPROX. DIMENSIONS Inches (Cm.) | | | APPROX. SHIP WEIGHT Lbs. (Kg.) | TYPE MTG. W – Wall F – Floor | KNOCKOUTS Inches (Cm.) | WEATHER SHIELD P/N | Wiring Diagrams & Design Figures Begin on Page 154 |
|------|-------------|------------------------------------|--------------|--------------|--------------------------------------|------------------------------------|---------------------------|--------------------------|--|
| | | HEIGHT | WIDTH | DEPTH | | | | | |
| 30.0 | TP131423S | 25.50 (64.8) | 24.39 (61.9) | 19.37 (49.2) | 299 (135.6) | F ① | NA | WSA1 | 69-E |
| 45.0 | TP131433S | 25.48 (64.7) | 24.39 (61.9) | 19.37 (49.2) | 353 (160.1) | F ① | NA | WSA1 | 69-E |
| 75.0 | TP131443S | 29.41 (74.7) | 28.15 (71.5) | 22.37 (56.8) | 463 (210.0) | F ① | NA | WSA2 | 69-E |

Notes: 30.0 through 75.0 kVA units TP1 compliant

GROUP Q

240 DELTA PRIMARY VOLTS — 480Y/277 SECONDARY VOLTS — 3Ø, 60 Hz

| kVA | CATALOG NO. | APPROX. DIMENSIONS Inches (Cm.) | | | APPROX. SHIP WEIGHT Lbs. (Kg.) | TYPE MTG. W – Wall F – Floor | KNOCKOUTS Inches (Cm.) | WEATHER SHIELD P/N | Wiring Diagrams & Design Figures Begin on Page 154 |
|-------|-------------|------------------------------------|--------------|--------------|--------------------------------------|------------------------------------|---------------------------|--------------------------|--|
| | | HEIGHT | WIDTH | DEPTH | | | | | |
| 15.0 | T3-796931S | 18.86 (48.0) | 20.30 (51.6) | 9.03 (22.9) | 245 (111.1) | F ① | NA | NA | 70-I |
| 30.0 | TP796944S | 25.50 (64.8) | 24.39 (61.9) | 19.37 (49.2) | 330 (149.7) | F ① | NA | WSA1 | 71-E |
| 45.0 | TP796954S | 25.48 (64.7) | 24.39 (61.9) | 19.37 (49.2) | 380 (172.4) | F ① | NA | WSA1 | 71-E |
| 75.0 | TP796964S | 29.41 (74.7) | 28.15 (71.5) | 22.37 (56.8) | 455 (206.4) | F ① | NA | WSA2 | 71-E |
| 112.5 | TP796974S | 35.47 (90.1) | 31.90 (81.0) | 26.88 (68.3) | 687 (311.6) | F | NA | WSA3 | 71-E |
| 150.0 | TP796984S | 41.52 (105.5) | 32.90 (83.6) | 29.87 (75.9) | 973 (441.3) | F | NA | WSA4 | 71-E |

Notes: 15 kVA unit encapsulated (TP1 exempt), 30.0 through 150.0 kVA TP1 compliant

① Wall mounting brackets are available for these sizes, refer to page 165.