



Actual

Catalog Number: CTL6-214
Product ID: 7TAH007200R0074
UPC Number: 78378613119
EAN Number: 05414363149965
Status: Active

Type CTL Copper Two-Hole Lug, Short Barrel, Max 35kV, Wire Size 6 Str or #6 Weld, 1/4 Inch Bolt Size, Tin Plated, Die Color Code Blue

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

North American Specifications (UNSPSC)

| | |
|------------------|--|
| UNSPSC | 39121405 Cable or wire lug |
| IGCC | 4532 Cable or wire lug |
| Brand Name | Blackburn |
| Type | Short Barrel Copper Lug |
| Special Features | Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance. |
| Standard | UL E9809 |
| Cable Size | 6 Str. |
| Stud Size | 1/4 Inch |
| Number Of Holes | 2 |
| Material | Copper |
| Color | Blue |

European Specifications (ETIM)

| | |
|------------------------|---|
| ETIM | EC001051 Tube cable lug for copper conductors |
| Connecting angle | Straight |
| Slender flange model | N |
| Insulated | N |
| With sight-hole | N |
| Material | Copper |
| Surface protection | Tinned |
| Number of fixing holes | 2 |

Packaging

| | |
|---------------------------|-------------------|
| Inner Quantity | 50 |
| Inner Dimensions (inches) | 3.3x2.8x2.3 |
| Outer Quantity | 500 |
| Outer Dimensions (inches) | 12.7x6.6x4.2 |
| Weight Uom | 1.88 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com