



Actual

Catalog Number: GG12
Product ID: 7TAA014230R0000
UPC Number: 78378680057
EAN Number: 05414363151845
Status: Active

Heavy Duty Ground Rod Clamps, Socket Set Screw, Nominal Rod Diameter 1/2, Wire Range 8 Sol - 2 Str

- Cast of high-strength corrosion-resistant copper alloy. Both hex head bolts and socket set screws available.
- Floating pressure bar distributes pressure evenly over large area of ground wire.

North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Ground Rod Clamps
Special Features	Cast of high-strength corrosion-resistant copper alloy. Both hex head bolts and socket set screws available.
Standard	CSA 12798
Conductor Size	8 sol - 2 str
Conductor Material	Copper

Packaging

Inner Quantity	50
Inner Dimensions (inches)	6.5x5x4.37
Outer Quantity	400
Weight Uom	12 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000478

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com